

**UNITRONIC® LAN 600 S/FTP Cat. 7 Y Flex
4x2xAWG 26/7**DB2170144
valid from: 05.09.2012**Application**

Flexible data cable for transmission of digital and analog signals up to 600 MHz. The cable is mainly designed for the use in the area of the workstation. According to TIA/EIA-568-B, ISO/IEC 11801 2nd edition, EN 50173, EN 50288-4-2, IEC 61156-6. For application in LANs like IEEE 802.3: 10Base-T, 100Base-T, 1000Base-T, 10GBase-T; FDDI; ISDN; ATM; Cable sharing.

Design

Conductor	bare copper AWG 26/7, stranded wire
Insulation	Skin-Foam-Skin PE, ca. 1.03 mm outer Ø
Core identification code	acc. to IEC 708-1
Pair screening	plastic laminated aluminium foil
Stranding	4 pairs, stranded to bundle
Screening	braid of copper wire, tinned wire ca. 0,10 mm
Outer sheath	PVC, grey similar to RAL 7035, outer Ø: ca. 6.2 mm

Electrical properties at 20° C

Resistance (loop)	max. 290 Ω/km, acc. to VDE 0812
Insulation resistance	min. 2 GΩxkm
Mutual capacitance	nom. 45 nF/km
Characteristic impedance	100 Ω ±5 Ω (at 100 MHz)
Velocity of propagation	ca. 0.78 c
Signal propagation time	<450 ns/100m
Delay difference	<10 ns/100m
Screening attenuation	>60 dB (up to 600 MHz)
Test voltage	700 V (AC)

**UNITRONIC® LAN 600 S/FTP Cat. 7 Y Flex
4x2xAWG 26/7**DB2170144
valid from: 05.09.2012**Transmission properties**

f [MHz]	Attenuation nom. [dB/100m]	NEXT nom. [dB]	ACR nom. [dB/100m]	ELFEXT nom. [dB/100m]	RL nom. [dB]
1	0.28	100	100	99	25
4	0.55	100	100	97	29
10	0.85	100	99	95	33
16	1.05	100	99	93	33
20	1.20	100	99	90	33
31.25	1.50	100	98	85	33
62.5	2.10	98	96	76	31
100	2.70	96	93	72	30
200	3.85	94	90	67	28
300	4.70	90	85	60	27
400	5.10	86	81	59	25
500	5.70	83	77	58	24
600	6.75	80	73	55	23

Mechanical and thermal properties

Minimum bending radius	during installation: 8 x cable Ø static: 4 x cable Ø
Permissible temperature range	during installation: 0° C up to +50° C static: -20° C up to +60° C
Flame propagation	flame retardant acc. to IEC 60332-1-2
General requirements	Dangerous and forbidden substances acc. to RoHS directive (2002/95/EG) are not allowed to the manufacturing.