


Product Description

Strain relief; Sealed by incised sealing ring; Corrosion-resistant; Decrease in installation height; Sea water-resistant



Application range

- Angled glands are used in areas where cables have to run in parallel to the housing wall.
- Electric motor manufacturing
- Machine and equipment manufacturing
- Plant engineering
- Light and sound applications

Benefits

- Strain relief
- Sealed by incised sealing ring
- Corrosion-resistant
- Decrease in installation height
- Sea water-resistant

Design

- Metric connection thread acc. to EN 50262

Note

- Counter nut to be used: SKINDICHT® SM-M

**Technical Data****Material**

Body: zinc die-casting, nickel-plated Compression
screw and hexagon nut: nickel-plated brass Incised
sealing ring: CR/NBR O-ring: NBR

Temperature range

-20°C to +100°C

Protection rating

IP 55

Article List

Part number	Article designation / size	Clamping range ØF (mm)	L	SW1	Ø A1	SW2	Ø A2	Ø G	Height (mm)	Overall length/ C (mm)	Thread length/ D (mm)	SW3	Pieces / PU
SKINDICHT® RWV-M													
52107800	12 x 1,5	5	20.5	14	16	12	13.2	8	5	26,1	11.5	17	25
52107810	16 x 1,5	9 - 3	23.5	18	20	16	17.6	12	5	28,6	11.5	22	25
52107820	20 x 1,5	13 - 4	28.5	22	24	20	22.2	15	5	35,1	12.5	27	25
52107830	25 x 1,5	17,5 - 8,5	31.0	27	29	25	27.5	20	5	38,1	13.5	32	10
52107840	32 x 1,5	25 - 16	33.0	34	36	32	35.2	27	5	44,6	13.5	41	10
52107850	40 x 1,5	32 - 23	43.0	42	45	40	43.5	35	5	53,1	15.5	46	5

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.