

## Product Description

Dimensionally stable;Flexible;Crush-resistant;Subsequent cable protection after cable installation;Fast and easy assembly



## Application range

- Vehicle construction
- Shipbuilding
- Mechanical engineering
- Electrical industry
- Used in areas where cables and wires need to be protected after assembly

## Benefits

- Dimensionally stable
- Flexible
- Crush-resistant
- Subsequent cable protection after cable installation
- Fast and easy assembly

## Design

- Divisible corrugated polyamide 6 conduit



**Note**

- UV-resistant and weather-resistant
- Upon request
- SILVYN® SPLIT PP (polypropylene) SILVYN® SPLIT NW 54/70

**Product features**

- Halogen and cadmium-free
- Abrasion-resistant
- High resistance to oil, petrol, acids and other chemicals

**Technical Data**

**Upon request**

SILVYN® SPLIT PP (polypropylene) SILVYN® SPLIT NW 54/70

**Colour delivered**

Black (RAL 9005), UV-resistant

**Material**

Halogen-free PA

**Protection rating**

IP 43 with SILVYN® SPLIT COV

**Temperature range**

-40 °C to +120 °C short-term 150°C

**Article List**

Part number	Article designation	Bending radius (mm)	Conduit size (mm)	For conduit with outer Ø (mm)	Suitable for SILVYN® COV	PU (m)
SILVYN® SPLIT						
61806621	8	70	6,2/11,2	11.2		50
61806620	10	55	8,9/13,6	13.6	M16/PG9	50
61806630	14	75	12,9/18,7	18.7	M20/PG13,5	50
61806631	16	100	10,3/15,8	15.8		50
61806640	20	105	19,8/25,9	25.9	M25/PG21	50
61806641	21	120	13,9/21	21.0		50
61806650	23	125	23,7/31,3	31.3	M32/PG29	50
61806651	32	180	26,2/34,5	34.5		50
61806660	37	170	31,7/41,9	41.9	M40/PG29	25



61806670	45	170	43,1/54,2	54.2	M50	25
----------	----	-----	-----------	------	-----	----

**Footnote:**

Photographs are not to scale and do not represent detailed images of the respective products.