
3M[™] Round Conductor Flat Cable

.050" 28 AWG Stranded, Halogen Free Insulation

2010 Series



- Advantage of this halogen free insulation are low smoke (BSS 7238) and low toxicity of combustion gases (NES 713) reducing the risk to firefighters and low corrosivity of combustion gases (pH≈6.0) reducing damage to nearby equipment
- 28 AWG stranded conductors on .050 inch pitch permits mass terminations to a broad line of IDC connectors
- Zippable for branching or discrete termination
- Please contact your 3M sales representative for variations not described in this specification
- RoHS* compliant

TS-0722-12
Date Modified: March 30, 2005

TS-0722-12
Sheet 1 of 2

Physical

Insulation

Material: Halogen Free Polyolefin (PO)

Color: off-white

Marking Standard: None

Conductors: 28 AWG 7×36 [7×0.127] Tinned Stranded Copper

Electrical

Voltage Rating: USA: 30V EU: <50V **Insulation Resistance:** >1 x $10^{10} \Omega /10$ ft [3 m]

UnbalancedBalancedCharacteristic Impedance: 107 Ω176 Ω

 Capacitance:
 14.0 pF/ft (45.93 pF/m)
 8.2 pF/ft (26.95 pF/m)

 Inductance:
 16 μH/ft (0.53 μH/m)
 .25 μH/ft (0.84 μH/m)

 Propagation Delay:
 1.50 ns/ft (4.92 ns/m)
 1.45 ns/ft (4.76 ns/m)

Velocity of Propagation: 68% 70%

Note: Unbalanced is measured between ground-signal-ground conductors. Balanced is measured between signal conductors within a pair.

Environmental

Temperature Rating: -20° C to +105° C

Flammabilty Rating: UL: Horizontal IEC 332-1, -2, & -3

*RoHS=Directive 2002/95/IEC,


Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment

UL File No.: E42769, Style No.: 20930

Number of Conductors	3M Part Number	Dimension A	Dimension B
09	2010/09	.450 ± .010 [11.43]	.400 ± .007 [10.16]
10	2010/10	.500 ± .010 [12.70]	.450 ± .007 [11.43]
14	2010/14	.700 ± .010 [17.78]	.650 ± .007 [16.51]
15	2010/15	.750 ± .010 [19.05]	.700 ± .007 [17.78]
16	2010/16	.800 ± .015 [20.32]	.750 ± .011 [19.05]
18	2010/18	.900 ± .015 [22.88]	.850 ± .011 [21.59]
20	2010/20	1.000 ± .015 [25.40]	0.950 ± .011 [24.13]
24	2010/24	1.200 ± .015 [30.48]	1.150 ± .011 [29.21]
25	2010/25	1.250 ± .015 [31.75]	1.200 ± .011 [30.48]
26	2010/26	1.300 ± .015 [33.02]	1.250 ± .011 [31.75]
30	2010/30	1.500 ± .020 [38.10]	1.450 ± .015 [36.83]
34	2010/34	1.700 ± .020 [43.18]	1.650 ± .015 [41.91]
36	2010/36	1.800 ± .020 [45.72]	1.750 ± .015 [44.45]
37	2010/37	1.850 ± .020 [46.99]	1.800 ± .015 [45.72]
40	2010/40	2.000 ± .020 [50.80]	1.950 ± .015 [49.53]
50	2010/50	2.500 ± .020 [63.50]	2.450 ± .015 [62.23]
60	2010/60	3.000 ± .020 [76.20]	2.950 ± .015 [74.93]

3.200 ± .020 [81.28]





2010/64

64

Inch [mm]

3.150 ± .015 [80.01]

Tolerance Unless Noted					
	.0	.00	.000		
Inch	±.1	±.01	±.005		

[] Dimensions for Reference only

1. Blue marking on one edge of cable designates wire #1.

Ordering Information

2010/XX Number of Conductors (See Table)

2. Available in standard lengths of 100 feet or 300 feet per roll, please specify when ordering.

TS-0722-12 Sheet 2 of 2

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of 1 year from the time of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.



Electronic Solutions Division

6801 River Place Blvd. Austin, TX 78726-9000 www.3M.com/esd

