

# **DATA SHEET**

0094000

ÖLFLEX® HEAT 260 SC

valid from:

04.02.2008

## **Application**

ÖLFLEX® HEAT 260 SC strands are heat resistant insulated wires used for wiring and connections in switch cabinets. Additional to the excellent mechanical and physical properties, ÖLFLEX® HEAT 260 SC single cores are characterized by very good electrical values, outstanding resistance against oil, weather and UV-radiation, as well as having high elasticity and tensile strength of the isolation material. ÖLFLEX® HEAT 260 SC strands are resistant against the action of water, acids, caustic solutions, solvents, synthetic liquids and oils. The cores are flame retardant.

#### Design

Conductor fine strands of silver plated copper wires

Core insulation PTFE compound 5YI1 in acc. to VDE 0207 part 6

## Electrical properties at 20 °C

Nominal voltage 300 V / 500 V

Test voltage 3400 V AC

### Mechanical and thermal properties

Temperature range -190 °C up to +260 °C max. conductor temperature

for short time up to +300 °C

Min. bending radius 4 x cable diameter for fixed installation

10 x cable diameter for flex. applications

Tests acc. to IEC 60811-x-x resp. VDE 0473 part 811-x-x and VDE 0472

EC directive this cable confirms to ECD 2006/95/EC (low voltage directive).