

Innovative metal and plastic housing design

Product Description

Housing in plastic or metal version. For power supply in the smallest possible space



Application range

- Machine and equipment manufacturing
- Control engineering
- Electronic laboratory

Benefits

- Housing in plastic or metal version. For power supply in the smallest possible space

Product features

- Surface-mount base
- 1 lever
- 1 cable entry
- Versions with / without cable gland
- Included: flat gasket

**Technical Data****Material**

Housing: powder-coated zinc die-casting, grey

Lever: zinc-plated steel Sealing: NBR

Housing: grey thermoplastic, black Lever:

zinc-plated steel Sealing: NBR

Protection rating

IP 65 (latched)

Temperature range

-40 °C to +100 °C, short-term up to +125 °C

Article List

Part number	Article	M	PG	Material	Colour	Cable gland	Cable clamping range	Dimensions incl. cable gland	Pieces / PU
H-A housing: surface-mount base									
10512700	H-A 3 MAgsv		11	Zinc die-casting	grey			51.5	10
10424000	H-A 3 Agsv		11	Thermoplastic	grey			56	10
10424500	H-A 3 MAgsv		11	Zinc die-casting	grey	yes	6,5 - 12	57.5	10
10424200	H-A 3 Agsv		11	Thermoplastic	grey	yes	6,5 - 12	65	10
19512700	H-A 3 MAgsv M20	20		Zinc die-casting	grey			54.5	10
19421900	H-A 3 Agsv M20	20		Thermoplastic	grey	yes	3 - 13,5	56	10
19424500	H-A 3 MAgsv M20	20		Zinc die-casting	grey	yes	3 - 13,5	60.5	10

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.