



Data Sheet

Type Number 6131
Designation IEC CR 11108
System Li-Manganese dioxide / Organic Electrolyte

UL Recognition:..... MH 13654 (N)
Nominal Voltage 3 V
Typical Capacity C 170 mAh
 Load 5.6 kOhm, at 20°C down to 2.0 V



Weight (approx.) 3 g
Volume 1,1 ccm
Coding..... TBA



Temperature Ranges min max.
 Storage -55°C 70°C
 Discharge -20°C 65°C

Dimensions min max.
 Diameter (A) 11,4 11,6
 Height (B) 10,4 10,8
 Shoulder Diameter[E]..... 7,8
 Shoulder Height [C]..... 0,4

Segment Electronic

Main Applications Photo
 Electronic

Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	2.0 V
Continuous 24h/d, 7d/w Current [µA]:	5600 Ω	Time: Capacity [mAh]: Energy [mWh]:	335 h 170 475

All Data contained herein is for single cells

For battery applications, performance data may vary from single cell data, depending on specific battery configuration

VARTA Microbattery GmbH, Daimlerstr. 1, D-73479 Ellwangen/Jagst
 Tel.: (+49) 7961/921-0, Telefax: (+49) 7961/921-553

Subject to change without prior notice!
 Date of issue:2004-12-16