

DATA SHEET

0162040

IEC compensating cable KN 91 L 2x0,5

valid from:

01.12.2008

Application

The compensating cable KN 91 L 2 x 0,5 mm² is a PVC insulated cable which transmits the thermoelectric voltage of NiCr/Ni thermocouples. It is for flexible use and fixed installation in dry and damp rooms. They may only be installed outdoors with UV protection and in observation of the max. permitted temperature range.

Design

Conductor 0,5 mm² (16 x 0,20 mm)

Conductor material KCA alloying, accuracy class 2 according IEC 60584

Positive conductor: Fe (iron)

Negative conductor: CuNi (cupronickel)

Core insulation PVC compound

Core identification Positive conductor: green

Negative conductor: white

Core layering Cores twisted together

Outer sheath PVC compound, colour: green

Electrical properties

Limiting deviation class 2 ± 100 μV (± 2,5 ℃) / m easuring point temperature +900 ℃

Mechanical and thermal properties

Temperature range occasional flexing: -5 ℃ up to +70 ℃

Minimum bending radius occasional flexing: 12 x cable diameter

Flammability flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2