






Date	SYM	REVISION RECORD	AUTH	DR.	CK.
03/09/12	E	ADDED INSULATOR OUTLINE IN PCB LAYOUT	T.B.	B.S.	
11/14/14	F	UPDATED TO ROHS 2 COMPLIANT	T.B.	B.S.	
07/17/15	G	DIM. 18.80 WAS 14.02 ADDED DIM. 23.11	T.B.	B.S.	



INSULATOR



PCB LAYOUT



SPECIFICATIONS:

- * Holder material- Polypropylene, AV161 PP, Off White
- * UL Flammability Rating: UL 94-HB File No. E108370
- * Contacts : Phosphor Bronze C5191, Nickel Plated 80-150u thickness
- * Vibration test: 10-50-10 hz swept in 60 seconds
x,y,z direction: 1 hour each direction
- * Result: no dislodgement of the cell or damage
no discontinuity over 10 micro-seconds
- * Shock test: half sine wave acceleration 150g.
6 micro-seconds 3 shock pulses each direction per axis,
total of 18 pulses
- * Result: no evidence of physical damage
- * ROHS 2 COMPLIANT

Tolerance (Except as noted)			
decimal $\pm .5$ (.020)	Scale	Drawn By B.S.	
Fractional $\pm .8$ (.030)	Approved By T.B.		
Angular $\pm 3^\circ$	Title	CR2032 SURFACE MOUNT BATTERY RETAINER WITH INSULATOR	
	Date	Drawing Number	
	07/17/15	BHX1-2032-SM	