


Date	SYM	REVISION RECORD	AUTH	DR.	CK.
10/12/07	C	UPDATED DIM. FOR PCB LAYOUT	T.B.	B.S.	
6/06/08	D	Temperature range was -40°C to +315°C	T.B.	B.S.	
2/26/10	E	Dim. 29.30 was 31.80	T.B.	B.S.	
3/05/10	F	Updated PCB Layout	T.B.	B.S.	
4/25/14	G	Updated to ROHS 2 compliant	T.B.	B.S.	



**SPECIFICATIONS:**

- \* Holder material- 30% glass reinforced Liquid Crystal Polymer resin, UL File No. E123598, UL94V-0
- \* Color: White
- \* Contacts : 0.020" thick PHOS-BRONZE, GOLD FLASH
- \* Temperature range: -40°C to +280°C
- \* Vibration Test: 10-50-10 Hz swept in 60 seconds  
X,Y,Z direction: 1 hour each direction
- \* Result: No dislodgement of the cell or damage  
No discontinuity over 10 micro-seconds
- \* Shock Test: Half sine wave acceleration 150G, 6 ms  
3 shock pulses each direction per axis, total of 18 pulses
- \* Result: No evidence of physical damage
- \* ROHS 2 COMPLIANT

Tolerance (Except as noted)			
decimal $\pm .5$ (.020)	Scale	Drawn By B.S.	
Fractional $\pm .8$ (.030)	Approved By T.B.		
Angular $\pm 3^\circ$	Title Date	Drawing Number	
	4/25/14	BU2032SM-JJ-GTR	