


Data Sheet



Type Number 390
Designation IEC SR54
System Silver oxide / Zinc /
 NaOH - Electrolyte

Nominal Voltage 1,55 V
Typical Capacity C 80 mAh
 Load 5.6 kOhm, at 20°C down to 1.3 V

Weight (approx.) 1,32 g
Volume 0,28 ccm
Coding..... Manufacturing Month/Year by
 Letter Code

Temperature Ranges

Storage	min	max.
Discharge	-10°C	65 °C
	-10°C	65°C

Dimensions

Diameter	min	max.
Height (A/B)	11,25	11,60
	2,75	3,05

Segment Watch

Main Applications Watch
 Photo
 Electronic

Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	1.2 V
Continuous	39000 Ω	Time:	290 h
24h/d,7d/w		Capacity [mAh]:	80
Current [μA]:	40	Energy [MWh]:	123