



## Non-Metallic Conduits

### • HG-PP PP Standard Weight

The standard conduit made from Polypropylene.

#### Features and Benefits

- resistant to acids and alkalis
- self-extinguishing

#### Application

Machine building, electrical installations, buildings, particularly when buried in concrete or plaster.



*HelaGuard PP Standard is typically used in electrical installations and buildings, particularly when buried in concrete or plaster.*

#### Material Data

Material	<b>Polypropylene (PP)</b>
Operating Temperature	<b>-20 °C to +90 °C</b>
Flammability	<b>self-extinguishing according to EN IEC 61386</b>



#### Technical Table

Article-No.	Type	Nominal Ø	Outside Ø	Inside Ø	Bending Radius	Weight (g/m)	Reel Length (m)	Colour
166-11900	<b>HG-PP10</b>	10	10.0	6.3	15	16	50	Black (BK)
166-11901	<b>HG-PP13</b>	13	13.0	9.8	25	20	50	Black (BK)
166-11902	<b>HG-PP16</b>	16	15.8	11.8	35	30	50	Black (BK)
166-11903	<b>HG-PP20</b>	20	20.0	14.8	40	45	50	Black (BK)
166-11904	<b>HG-PP21</b>	21	21.2	16.7	40	50	50	Black (BK)
166-11905	<b>HG-PP25</b>	25	25.0	19.1	50	60	50	Black (BK)
166-11906	<b>HG-PP26</b>	26	25.4	21.4	50	52	50	Black (BK)
166-11907	<b>HG-PP28</b>	28	28.5	22.8	55	65	50	Black (BK)
166-11908	<b>HG-PP34</b>	34	34.5	28.1	65	90	25	Black (BK)
166-11909	<b>HG-PP42</b>	42	42.5	35.5	80	120	25	Black (BK)
166-11910	<b>HG-PP54</b>	54	54.5	47.2	100	150	25	Black (BK)
166-11911	<b>HG-PP67</b>	67	67.2	56.3	150	250	10	Black (BK)

All dimensions in mm. Subject to technical changes.

Colour grey available on request.

Other reel lengths available on request.