


# DATASHEET

## Enamelled Copper Wire

Version 11/17

### Enamelled Copper Wire



#### Specification

Copper Wire  
Enamel  
Temperature

2UEWF  
PU class 155  
155°C max.

#### Technical Data

Length:	Item no.	Wire Diameter(mm)	Enamel/PU coating thickness(mm)	Resistance( $\Omega$ /km)	Rated Voltage(kv)
1500 M	604975	0.05 $\pm$ 0.015	0.008-0.019	10240	0.30
450 M	605090	0.01 $\pm$ 0.018	0.01-0.025	2381	0.50
220 M	605196	0.15 $\pm$ 0.02	0.012-0.027	1037	1.00
110 M	605322	0.2 $\pm$ 0.023	0.016-0.031	577.2	1.50
50 M	605426	0.3 $\pm$ 0.04	0.02-0.037	254	2.00
35 M	605486	0.4 $\pm$ 0.05	0.022-0.039	141.7	2.20
23 M	605544	0.5 $\pm$ 0.065	0.024-0.42	89.95	2.50
9 M	605604	0.8 $\pm$ 0.085	0.03-0.052	35.17	2.80
6M	605660	1 $\pm$ 0.1	0.034-0.062	22.49	3.00

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represent the technical status at the time of printing.

© Copyright 2016 by Conrad Electronic SE.