

Data sheet Polytronik® Toroidal transformer

Part no.: RSO 825014

Description: RKT 50VA/ 230V/ 2x12.0V 2x2.08A

Safety isolating transformer according to: EN 61558-2-6 / VDE 0570

Power [VA]: 5

Input voltage [AC]:

Output voltage [AC]:

Output current [AC]:

Prequency [Hz]:

Dielectric strength PRI - SEC [AC]:

Efficiency [%]:

Power loss at no-load [W]:

230 V +-10%

2 x 12.00 V

2 x 2.08 A

50/60

4400 V

86

0.49

Maximum ambient temperature ta [°C]: 60


Temperature class: B (130°C)

Temperature switch: 120°C (automatically resetting)





Schematic:



possible interconnections: parallel connection 12.0V / 4.17A = connect black with violet and red with white

series connection 24.0V / 2.08A = connect red with violet

Approval marks: CE; ENEC; UL508 (E182061)

Connections: primary and secondary strands 200mm long, ends assembled with ferrules

Model: toroidal transformer pottet on mounting disc with through-hole 5.5 mm

Appliance class: prepared for class II

Protection class: IP 00

Recommended fuse ratings: primary 0.400 AT (IEC60127-2-5)

secondary 1 2.50 AT (IEC60127-2-3) secondary 2 2.50 AT (IEC60127-2-3)

Dimensions: diameter approx. = 78 mm

height approx. = 42 mm

Weight: approx. 0.68 kg

<u>www.sedlbauer.de</u> Status: August 2017