

**EDWANZ** group

## Data sheet Polytronik® Toroidal transformer

Part no.: RSO 825019

Description: RKT 75VA/ 230V/ 2x9.0V 2x4.17A

Safety isolating transformer according to: EN 61558-2-6 / VDE 0570

Power [VA]:

Input voltage [AC]: 230 V +-10% Output voltage [AC]: 2 x 9.00 V Output current [AC]: 2 x 4.17 A Frequency [Hz]: 50/60 Dielectric strength PRI - SEC [AC]: 4400 V Efficiency [%]: 86 0.58 Power loss at no-load [W]: Maximum ambient temperature ta [°C]: 60

Temperature class: B (130°C)

Temperature switch: 120°C (automatically resetting)





## Schematic:



possible interconnections: parallel connection 9.0V / 8.34A = connect black with violet and red with white

series connection 18.0V / 4.17A = connect red with violet

Approval marks: CE; ENEC; UL508 (E182061)

Connections: primary and secondary strands 200mm long, ends assembled with ferrules

Model: toroidal transformer pottet on mounting disc with through-hole 6.3 mm

Appliance class: prepared for class II

Protection class: IP 00

Recommended fuse ratings: primary 0.630 AT (IEC60127-2-5)

secondary 1 5.00 AT (IEC60127-2-3) secondary 2 5.00 AT (IEC60127-2-3)

Dimensions: diameter approx. = 92 mm

height approx. = 40 mm

Weight: approx. 0.92 kg

www.sedlbauer.de Status: August 2017