



Data sheet Polytronik® Toroidal transformer

Part no.:	RSO 825007
Description:	RKT 30VA/ 230V/ 2x9.0V 2x1.67A
Safety isolating transformer according to:	EN 61558-2-6 / VDE 0570
Power [VA]:	30
Input voltage [AC]:	230 V +-10%
Output voltage [AC]:	2 x 9.00 V
Output current [AC]:	2 x 1.67 A
Frequency [Hz]:	50/60
Dielectric strength PRI - SEC [AC]:	4400 V
Efficiency [%]:	86
Power loss at no-load [W]:	0.41
Maximum ambient temperature t_a [°C]:	60
Temperature class:	B (130°C)
Temperature switch:	120°C (automatically resetting)



Schematic:



possible interconnections: parallel connection **9.0V / 3.34A** = connect black with violet and red with white
 series connection **18.0V / 1.67A** = connect red with violet

Approval marks:	CE; ENEC; UL508 (E182061)
Connections:	primary and secondary strands 200mm long, ends assembled with ferrules
Model:	toroidal transformer potted on mounting disc with through-hole 5.5 mm
Appliance class:	prepared for class II
Protection class:	IP 00
Recommended fuse ratings:	primary 0.250 AT (IEC60127-2-5) secondary 1 2.00 AT (IEC60127-2-3) secondary 2 2.00 AT (IEC60127-2-3)
Dimensions:	diameter approx. = 69 mm height approx. = 39 mm
Weight:	approx. 0.51 kg