


Reihenlüsterklemme, 12-polig, 6 mm<sup>2</sup>, mit Polabdeckung  
 Terminal block, 12-way, 6 mm<sup>2</sup>, with pole cover




### Beschreibung / Description


–

### Technische Daten / Specification

Nennspannung / Rated voltage	400 VAC
Nennstrom / Rated current	16 A
Bauart / According to	DIN EN 60598 / DIN EN 60998-2-1
Anschlüsse / Type of terminals	Schraubanschluss / Screw terminals
Kontakte / Material of terminals	CuZn 39
Kontaktträger / Carrying parts	Polyethylen / Polyethylene
Gehäuse / Cover	Polyethylen / Polyethylene

### Abmessungen / Dimension





Reihenlüsterklemme 12-polig, 6,0 mm<sup>2</sup>  
mit Polabdeckung

*Terminal block 12-way 6sq.  
with pole cover*

Typ: 636  
*Type:*

Nennspannung: AC 400 V  
*Rated voltage:*

Nennstrom: 16 A  
*Rated current:*

Bauart: DIN EN 60598  
*According to:* DIN EN 60998-2-1

Schutzart: IP 20  
*IP-Code*

Anschlüsse: Schraubanschlußklemmen  
*Type of Terminals:* screw-type terminals

Kontakte: CuZn 39  
*Material of Terminals:*

Kontaktträger: Polyethylen  
*Carrying parts:* Polyethylene

Gehäuse: Polyethylen  
*Cover:* Polyethylene

Approbationen: —  
*Certified by:*

Anmerkung: —  
*Annotation:*