

397 0% MERCURY

SR726SW (SR59) Watch Battery OEM Swiss Made

Technical Data Sheet

Specifications

Chemical system Zinc / Monovalent Silver Oxide, low drain

Nominal Voltage 1,55 V

Capacity 32 mAh, Discharge over 25,5 kΩ at 20 °C to 1,2 V

Operating Temperature 0°C − 60°C


Self Discharge Less than 5% per year at 20 ℃

Weight ~0,48 g

Dimensions


(according IEC 60086-3)

Diameter 7,90 mm (0,457") Height 2,60 mm (0.102")



Discharge Curve

Constant Load 25,5 k Ω Starting Drain 60,7 μ A Temperature 20 $^{\circ}$ C



Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative. For safety related information please consult the PSDS document related to that product or product family.

Rev. 397MF_OEM.04 2013/02