



Type Number..... 4626
Designation IEC..... LR9
System..... Manganese Dioxide/
 Zinc/KOH-Electrolyte

Nominal Voltage..... 1,5V
Typical Capacity C..... 120 mAh
 Load 300 Ω, at 20°C down to 0.9 V

Coding..... Manufacturing Month/Year
 by Letter Code

Temperature Ranges min max.
 Storage..... -10°C 65°C
 Discharge..... -10°C 65°C

Dimensions min max.
 Diameter..... 15,20 16,00
 Height (A/B)..... 5,06 6,20

Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	0.9V
Continuous 24h/d, 7d/w	300 Ω	Time:	29 h
		Capacity:	120 mAh

All Data contained herein is for single cells
 For battery applications, performance data may vary from single cell data, depending on specific battery configuration

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries