

RJ11 socket insert - VS-RJ11-BU-MOD/BU - 1656356

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Socket insert RJ11, modular system (Keystone), 6-pos., unshielded

Key commercial data

package_quantity	1
GTIN	4046356029803

Technical data

Mechanical characteristics

Number of positions	6
Number of slots	1
Shielded	No
Connection method	female

Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
Degree of protection	IP20

Material data

Inflammability class according to UL 94	V0
Contact carrier material	Thermoplastic
Contact material	Copper alloy
Contact surface material	Gold over nickel

Electrical characteristics

Number of positions	6
Transmission characteristics (category)	CAT3

classifications

eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260705

RJ11 socket insert - VS-RJ11-BU-MOD/BU - 1656356

classifications

eCl@ss

eCl@ss 7.0	27440309
eCl@ss 8.0	27440309

ETIM

ETIM 2.0	EC000438
ETIM 3.0	EC000438
ETIM 4.0	EC000438
ETIM 5.0	EC000438

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

approvals

GOST /


Approval details

 GOST
--

Drawings

RJ11 socket insert - VS-RJ11-BU-MOD/BU - 1656356

Dimensioned drawing



RJ11 female insert

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>