

Surge protection device - DT-UFB-485/BS - 2920612

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



9-pos. D-SUB attachment plug with surge protection for RS-485 interfaces. Can alternatively be snapped onto DIN rails.

Product Features

- ☒ Adapter type
- ☒ 9-pos. D-SUB connection
- ☒ DIN rail mounting possible by removing the cap



Key commercial data

package_quantity	1
GTIN	4046356155120

Technical data

Dimensions

Height	110 mm
Width	25 mm
Depth	63 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Degree of protection	IP20

General

Housing material	Zinc die-cast
Color	silver/black
Standards for air and creepage distances	IEC 60664-1
Standards for air and creepage distances	VDE 0110-1
Mounting type	Connection-specific attachment plug and DIN rail, 35 mm
Design	Attachment plug for DIN rail mounting
Number of positions	5
Direction of action	Line-Line & Line-Ground/Shield

Protective circuit

IEC test classification	B2
-------------------------	----

Surge protection device - DT-UFB-485/BS - 2920612

Technical data

Protective circuit

IEC test classification	C1
IEC test classification	C2
IEC test classification	C3
IEC test classification	D1
VDE requirement class	B2
VDE requirement class	C1
VDE requirement class	C2
VDE requirement class	C3
VDE requirement class	D1
Maximum continuous operating voltage U_c	12 V DC
Maximum continuous voltage U_C (wire-wire)	12 V DC
Maximum continuous voltage U_c (wire-ground)	90 V DC
Nominal current I_N	≤ 380 mA (25 °C)
Operating effective current I_c at U_c	≤ 1 μ A
Residual current I_{pE}	≤ 5 μ A
Nominal discharge current I_n (8/20) μ s (Core-Core)	≤ 5 kA
Nominal discharge current I_n (8/20) μ s (Core-Earth)	≤ 5 kA
Total surge current (8/20) μ s	10 kA
Output voltage limitation at 1 kV/ μ s (Core-Earth) spike	≤ 700 V
Output voltage limitation at 1 kV/ μ s (Core-Core) static	≤ 25 V
Output voltage limitation at 1 kV/ μ s (Core-Earth) static	≤ 700 V
Output voltage limitation at 1 kV/ μ s (Core-GND) static	≤ 25 V
Residual voltage at I_n , (conductor-conductor)	≤ 25 V
Residual voltage at I_n , (conductor-ground)	≤ 55 V
Residual voltage at I_n , (conductor-GND)	≤ 25 V
Voltage protection level U_p (Core-Core)	≤ 30 V (B2 - 100 A)
Voltage protection level U_p (Core-Core)	≤ 30 V (C1 - 500 A)
Voltage protection level U_p (Core-Core)	≤ 40 V (C2 - 5 kA)
Voltage protection level U_p (Core-Earth)	≤ 700 V (B2 - 100 A)
Voltage protection level U_p (Core-Earth)	≤ 700 V (C1 - 500 A)
Voltage protection level U_p (Core-Earth)	≤ 750 V (C2 - 5 kA)
Response time t_A (Core-Core)	≤ 100 ns
Response time t_A (Core-Earth)	≤ 100 ns
Input attenuation a_E , sym.	typ. 0.3 dB (≤ 30 MHz)
Input attenuation a_E , sym.	typ. 0.3 dB (≤ 7 MHz / 150 Ω)
Input attenuation a_E , sym.	typ. 0.3 dB (≤ 2 MHz / 600 Ω)
Cut-off frequency f_g (3 dB), sym. in 100 Ohm system	typ. 50 MHz
Resistance in series	3.3 Ω 10 %
Surge carrying capacity in acc. with IEC 61643-21 (Core-Core)	C1 (1 kV / 500 A)
Surge carrying capacity in acc. with IEC 61643-21 (Core-Core)	C2 (10 kV/5 kA)

Surge protection device - DT-UFB-485/BS - 2920612

Technical data

Protective circuit

Surge carrying capacity in acc. with IEC 61643-21 (Core-Core)	B2 (4 kV / 100 A)
Surge carrying capacity in acc. with IEC 61643-21 (Core-Earth)	B2 (4 kV / 100 A)
Surge carrying capacity in acc. with IEC 61643-21 (Core-Earth)	C1 (1 kV / 500 A)
Surge carrying capacity in acc. with IEC 61643-21 (Core-Earth)	C2 (10 kV/5 kA)
Surge carrying capacity in acc. with IEC 61643-21 (Core-Earth)	D1 (1 kA)

Connection data

Connection method	D-SUB-9
Connection type IN	D-SUB-9 socket
Connection type OUT	D-SUB-9 connector

Connection, equipotential bonding

Connection method	Cable connection
-------------------	------------------

Standards and Regulations

Standards/regulations	IEC 61643-21
Standards/regulations	DIN EN 61643-21

classifications

eCl@ss

eCl@ss 4.0	27140201
eCl@ss 4.1	27130801
eCl@ss 5.0	27130801
eCl@ss 5.1	27130801
eCl@ss 6.0	27130807
eCl@ss 7.0	27130807
eCl@ss 8.0	27130807

ETIM

ETIM 2.0	EC000943
ETIM 3.0	EC000943
ETIM 4.0	EC000943
ETIM 5.0	EC000943

UNSPSC

UNSPSC 6.01	30212010
UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610
UNSPSC 13.2	39121620

Surge protection device - DT-UFB-485/BS - 2920612

approvals

GOST / GOST /

Approval details



accessories


Data cable preassembled

VS-09-DSUB-20-LI-1,0 - 1656233




Drawings

Dimensioned drawing



Surge protection device - DT-UFB-485/BS - 2920612

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>