

CERTIFICATE

Issued to:
Applicant:
Hans Wagner GmbH
Brunnenstrasse 2
96358 Reichenbach/ofr, Germany

Licensee:
Hans Wagner GmbH
Brunnenstrasse 2
96358 Reichenbach/ofr, Germany

Product : 2-pole plug for class I appliances
Trade name(s) : HAWA
Type(s)/model(s) : B1.

The product and any acceptable variation thereof as specified in the Annex to this certificate and the documents referred to therein.

DEKRA hereby declares that the above-mentioned product has been certified based on:

- a type test according to IEC 60884-1:2022, NEN 1020:2019, NEN-IEC 60884-1:2019, NEN-IEC 60884-1:2019/A1:2019, NEN-IEC 60884-1:2019/A2:2019, DIN VDE 0620-2-1:2021-02, DIN VDE 0620-2-1:2021-02/A1:2023-09 and DIN VDE 0620-2-1:2021-02/A2:2025-10
- an inspection of the factory location according to CENELEC Operational Document CIG 421
- a DEKRA certification agreement with the number 6071845


DEKRA hereby grants the right to use the DEKRA Mark.

The DEKRA Mark may be applied to the product as specified in this certificate for the duration and under the conditions of the DEKRA Mark certification agreement.

This certificate is issued on 25 August 2026 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 71-181557

DEKRA Certification B.V.



B.T.M. Holtus
Managing Director



Henk Schendstok
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL



71-181557

DEKRA Mark is the new KEMA-KEUR

The DEKRA Mark certificate for this product is to all intents and purposes equivalent to a KEMA-KEUR certificate, the other certification mark used by DEKRA and should be valued and used as such. DEKRA Mark is gradually replacing KEMA-KEUR.

For more information please check: [Introducing DEKRA Mark](#)

SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

Product	: 2-pole plug for class I appliances
Trade name(s)	: HAWA
Type(s)/model(s)	: B1.
Rated current	: 16 A
Rated voltage	: 250 V~
Earthing	: with dual earthing contacts
Design	: non-rewirable
Standard sheet	: VII
Applied flexible cord	: H03VV-F 3G0,75 mm ² H05VV-F 3G0,75, 3G1,0 and 3G1,5 mm ² H05V2V2-F 3G0,75, 3G1,0 and 3G1,5 mm ² H05RN-F 3G1,0 mm ²
Certification mark	: complies with the specified requirements
Cord termination	: crimped connection
Description	: body of thermoplastic material as part of a complete or incomplete cord set for class I appliances

List of components

Component	Manufacturer/ Trade name	Type/Model	Approval mark ¹⁾
insert	P.G.R. s.r.l.	PFT480P2 (solid pins)	*

¹⁾ * indicates a component tested as part of the appliance

TESTS**Test requirements**

IEC 60884-1:2022
NEN 1020:2019
NEN-IEC 60884-1:2019
NEN-IEC 60884-1:2019/A1:2019
NEN-IEC 60884-1:2019/A2:2019
DIN VDE 0620-2-1:2021-02
DIN VDE 0620-2-1:2021-02/A1:2023-09
DIN VDE 0620-2-1:2021-02/A2:2025-10

Test result

The test results are documented in DEKRA test file 229667600.

Conclusion

The examination has confirmed that all requirements were met.

Factory location

Hans Wagner GmbH
Birkenstrasse 14
96358 Reichenbach, Germany