

Ferrule - A 4 - 9 - 3200302

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Ferrule, Length: 9 mm, Color: silver

The figure shows variant A 1-6

Product Features

- The A 0,25.. ferrules can also be used to process 0.14 mm² conductors
- The dimensions of the ferrules conform to DIN 46228-1
- The ferrules without plastic sleeve are made from soft tin-plated electrolytic copper

Key commercial data

| | |
|-------------------------|---------------|
| package_quantity | 1000 |
| GTIN | 4017918093952 |

Technical data

Dimensions

| | |
|---|--------|
| Length (b) | 9 mm |
| Sleeve length | 8 mm |
| Inner dimension of the insulating collar (d) | 4 mm |
| Ferrule diameter | 2.8 mm |
| Sleeve wall thickness | 0.2 mm |

Ambient conditions

| | |
|-----------------------------------|--------|
| Max. permanent temperature | 105 °C |
|-----------------------------------|--------|

General

| | |
|-----------------|--------|
| Color | silver |
| Material | E-CU |

classifications

eCl@ss

| | |
|-------------------|----------|
| eCl@ss 4.0 | 27060701 |
| eCl@ss 4.1 | 27060701 |
| eCl@ss 5.0 | 27400201 |
| eCl@ss 5.1 | 27400201 |
| eCl@ss 6.0 | 27400201 |

Ferrule - A 4 - 9 - 3200302

classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 7.0 | 27400201 |
| eCl@ss 8.0 | 27400201 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000005 |
| ETIM 3.0 | EC000005 |
| ETIM 4.0 | EC000005 |
| ETIM 5.0 | EC000005 |


UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30212109 |
| UNSPSC 7.0901 | 27121703 |
| UNSPSC 11 | 27121703 |
| UNSPSC 12.01 | 27121703 |
| UNSPSC 13.2 | 27121703 |

approvals

CSA / CSAus / cCSAus /

Approval details

| | |
|---|--|
|  | |
| Nominal voltage UN | |
| Nominal current IN | |
| mm ² /AWG/kcmil | |

| | |
|----------------------------|--|
| CSAus | |
| Nominal voltage UN | |
| Nominal current IN | |
| mm ² /AWG/kcmil | |

| |
|---------------|
| cCSAus |
|---------------|

Drawings