

# CERTIFICATE

Issued to:  
Applicant:  
**Hans Wagner GmbH**  
**Brunnenstrasse 2**  
**96358 Reichenbach/ofr, Germany**

Licensee:  
**Hans Wagner GmbH**  
**Brunnenstrasse 2**  
**96358 Reichenbach/ofr, Germany**

Product : 2-pole connector  
Trade name(s) : HAWA  
Type(s)/model(s) : D1

The product and any acceptable variation thereof as specified in the Annex to this certificate and the documents referred to therein.

DEKRA hereby declares that the above-mentioned product has been certified based on:

- a type test according to EN IEC 60320-1:2021
- an inspection of the factory location according to CENELEC Operational Document CIG 021
- a DEKRA certification agreement with the number 2121597


DEKRA hereby grants the right to use the ENEC certification mark.

The ENEC certification mark may be applied to the product as specified in this certificate for the duration and under the conditions of the ENEC certification agreement.

This certificate is issued on 2 August 2024 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 71-111858 REV.1

DEKRA Certification B.V.



B.T.M. Holtus  
Managing Director



H.R.M. Barends  
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE  
DUTCH ACCREDITATION  
COUNCIL



**SPECIFICATION OF THE CERTIFIED PRODUCT****Product data**

|                       |                                                                                                      |
|-----------------------|------------------------------------------------------------------------------------------------------|
| Product               | : 2-pole connector                                                                                   |
| Trade name(s)         | : HAWA                                                                                               |
| Type(s)/model(s)      | : D1                                                                                                 |
| Rated current         | : 10 A                                                                                               |
| Rated voltage         | : 250 V~                                                                                             |
| Standard sheet        | : C13 of EN 60320-3                                                                                  |
| Temperature limit     | : T70                                                                                                |
| Overvoltage category  | : II                                                                                                 |
| Pollution degree      | : 2                                                                                                  |
| Earthing              | : with earthing contact                                                                              |
| Design                | : non-rewirable                                                                                      |
| Applied flexible cord | : see list of components                                                                             |
| Cord termination      | : crimped connection                                                                                 |
| Description           | : body of thermoplastic material as part of a complete or incomplete cord set for class I appliances |

**List of components**

| Component     | Manufacturer/<br>Trade name | Type/Model                     | Approval mark <sup>1)</sup> |
|---------------|-----------------------------|--------------------------------|-----------------------------|
| insert        | P.G.R. S.r.l.               | PCE23                          | *                           |
| flexible cord | KORDES KABEL                | H05VV-F 3G0,75 mm <sup>2</sup> | VDE HAR                     |
| flexible cord | KORDES KABEL                | H05VV-F 3G1,0 mm <sup>2</sup>  | VDE HAR                     |
| flexible cord | KORDES KABEL                | H05VV-F 3G1,5 mm <sup>2</sup>  | VDE HAR                     |

<sup>1)</sup> \* indicates a component tested as part of the appliance

**TESTS****Test requirements**

EN IEC 60320-1:2021

**Test result**

The test results are documented in DEKRA test file 228909700.

**Additional information**

This certificate replaces certificate No. 71-111858 which we hereby declare invalid.

**Conclusion**

The examination has confirmed that all requirements were met.

**Factory location**

Hans Wagner GmbH  
Birkenstrasse 14  
96358 Reichenbach, Germany