



Residual current circuit-breaker, 25A, 4pole, 30mA, type A



Part no. PXF-25/4/003-A
Catalog No. 236772

Similar to illustration

Delivery program

Basic function			Residual current circuit-breakers
Number of poles			4 pole
Application			Switchgear for residential and commercial applications
Rated current	I_n	A	25
Rated short-circuit strength	I_{cn}	kA	10
Rated fault current	$I_{\Delta N}$	A	0.03
Type			Type A
Tripping		s...	non-delayed
Product range			PXF
Sensitivity			Pulse-current sensitive
Impulse withstand current			Partly surge-proof 250 A

Technical data

Electrical

Standards			IEC/EN 61008
Rated operational voltage	U_e	V	
	U_e	V AC	
Rated operating voltage	U_e	V AC	230/400
Rated frequency	f	Hz	50
Limit values of the operating voltage			
Test circuit		V AC	184 - 440
Comment for range of the test button			3-phase application without N (400V AC Phase-Phase) not allowed
Sensitivity			Pulse-current sensitive
Rated insulation voltage	U_i	V	440
Rated impulse withstand voltage	U_{imp}	kV	4
Rated short-circuit strength	I_{cn}	kA	10
Rated making and breaking capacity / Rated residual making and breaking capacity	$I_m / I_{\Delta m}$	A	500
lifespan			
Electrical	Operations		≥ 4000
Mechanical	Operations		≥ 20000

References

Auxiliary switch for subsequent installation			Z-HK 248432
Tripping signal contact for subsequent installation			Z-NHK 248434
Remote control and automatic switching device			Z-FW/LP 248296
Compact enclosure			KLV-TC-4 276241
Switching interlock			IS/SPE-1TE 101911
Sealing cover set			Z-RC/AK-4MU 101062

Mechanical

Standard front dimension		mm	45
Device height		mm	80
Built-in width		mm	70 (4TE)
Mounting			Quick attachment with 2 latch positions for DIN-rail IEC/EN 60715
Degree of Protection			IP20, IP40 with suitable enclosure
Terminals top and bottom			Open mouthed/lift terminals
Terminal protection			DGUV VS3, EN 50274

Terminal cross-section			
Solid		mm ²	1.5 - 35
Stranded		mm ²	2 x 16
Thickness of busbar material		mm	0.8 - 2
Permissible storage and transport temperatures		°C	-35 - +60
Climatic proofing			25-55°C/90-95% relative humidity according to IEC 60068-2

Design verification as per IEC/EN 61439

Technical data for design verification			
Rated operational current for specified heat dissipation	I _n	A	25
Heat dissipation per pole, current-dependent	P _{vid}	W	0
Equipment heat dissipation, current-dependent	P _{vid}	W	3.1
Static heat dissipation, non-current-dependent	P _{vs}	W	0
Heat dissipation capacity	P _{diss}	W	0
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	55
			Starting at 40 °C, the max. permissible continuous current decreases by 3% for every 1 °C
IEC/EN 61439 design verification			
10.2 Strength of materials and parts			
10.2.2 Corrosion resistance			Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures			Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat			Meets the product standard's requirements.
10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects			Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation			Meets the product standard's requirements.
10.2.5 Lifting			Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact			Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions			Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES			Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances			Meets the product standard's requirements.
10.5 Protection against electric shock			Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components			Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections			Is the panel builder's responsibility.
10.8 Connections for external conductors			Is the panel builder's responsibility.
10.9 Insulation properties			
10.9.2 Power-frequency electric strength			Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage			Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material			Is the panel builder's responsibility.
10.10 Temperature rise			The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function			The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Residual current circuit breaker (RCCB) (EC000003)			
Electric engineering, automation, process control engineering / Electrical installation, device / Residual current protection system / Residual current circuit breaker (RCCB) (ecl@ss10.0.1-27-14-22-01 [AAB906014])			
Number of poles			4
Rated voltage		V	400
Rated current		A	25
Rated fault current		mA	30
Rated insulation voltage Ui		V	440

Rated impulse withstand voltage U _{imp}	kV	4
Mounting method		DIN rail
Leakage current type		A
Selective protection		No
Short-time delayed tripping		No
Short-circuit breaking capacity (I _{cw})	kA	10
Surge current capacity	kA	0.25
Frequency		50 Hz
Additional equipment possible		Yes
With interlocking device		Yes
Degree of protection (IP)		IP20
Width in number of modular spacings		4
Built-in depth	mm	70.5
Ambient temperature during operating	°C	-25 - 55
Pollution degree		2
Connectable conductor cross section multi-wired	mm ²	1.5 - 16
Connectable conductor cross section solid-core	mm ²	1.5 - 35