


<b>Nominal Voltage:</b>	1.5 V
<b>Operating Voltage</b>	1.6 -0.75V
<b>Impedance:</b>	130 m-ohm @ 1kHz
<b>Typical Weight:</b>	71 gm (2.5 oz.)
<b>Typical Volume:</b>	26.9 cm <sup>3</sup> (1.6 in. <sup>3</sup> )
<b>Terminals:</b>	Flat
<b>Storage Temperature Range:</b>	-20°C to 35°C
<b>Operating Temperature Range:</b>	-20°C to 54°C (-4°F to 130°F)
<b>ANSI:</b>	14A
<b>IEC:</b>	LR14

TYPICAL DISCHARGE CHARACTERISTICS AT 21°C (70°F)




## DURACELL® BATTERIES


Berkshire Corporate Park  
Bethel, CT 06801 U.S.A.  
Telephone: Toll-free 1-800-544-5454  
Internet: www.duracell.com

\* Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.


DELIVERED ENERGY VS POWER DRAIN



DELIVERED CAPACITY VS POWER DRAIN



SERVICE HOURS VS POWER DRAIN



All testing at 21°C (70°F)

## DURACELL<sup>®</sup> BATTERIES

Berkshire Corporate Park  
Bethel, CT 06801 U.S.A.  
Telephone: Toll-free 1-800-544-5454  
Internet: [www.duracell.com](http://www.duracell.com)

\* Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.