

型 號

Model No.

R13-2

動 作 特 性
Circuit

2P SPST ON-OFF

規 格
Rating

3A 125V, 1.5A 250V AC

接 觸 電 阻
Contact resistance

50mΩ Max





絕 緣 電 阻
Insulation resistance

DC 500V 100MΩ Min

耐 電 壓
Dielectric strength

AC 1000V 1 minute

Rating	3A 125V AC/1.5A 250V AC	Mount Hole	Circuit Structure
Contact R	50m ohm Max.		
Insulation R	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1000V 1 minute		
Circuit	2P SPST ON-OFF		



C1\WK12\R13-2.DWG

▲	09/13/01	張曉斌	更正圖面錯誤				
△	Date	Name	Descriptions				
Drawing	Check	Approval	SCI No.		Model Name		
張曉斌	<i>張曉斌</i>	<i>李喜耀</i>	Customer No.		Model No.	R13-2	
09/13/01	9/13/01	9/13/01	Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.		