



Material Safety Data Sheet

1. Product & Company Identification

| | |
|-------------------------|--|
| Product: | Non-Rechargeable Alkaline Button Cell Set AG 1 (LR621, 364); AG 2 (LR726, 397); AG 3 (LR41, 392); AG 4 (LR626, 377); AG 5 (LR754, 393); AG 6 (LR921, 371); AG 7 (LR926, 395); AG 8 (LR1120, 391); AG 9 (LR936, 394); AG 10 (LR54, 389); AG 11 (LR721, 362); AG 12 (LR43, 386); AG 13 (LR44, 357). |
| Manufacturer: | Conrad Electronic SE |
| Nominal voltage: | 1,5 V |
| Address: | Klaus-Conrad-Str. 1, D-92240 Hirschau |
| Telephone: | +49 (0) 9604 / 40 - 8988 |
| Date of issue: | 29.09.2016 |

2. Ingredients

| Hazardous Components (Specific Chemical Identity, Common Names), Compiled with 98/101/EEC & 91/157/EEC | Specification (%) |
|--|-------------------|
| Mercury Content | < 0.0001 |
| Cadmium Content | < 0.001 |
| Lead Content | < 0.001 |

3. Hazards Identification

| | |
|---|---|
| Boiling Point | KOH aqua solution = 140 degree Celsius |
| Specific Gravity (H2O = 1) | MnO2 = 4.4, Zn = 7.1, KOH = 2.0 |
| Vapor Pressure (mm Indium) | KOH aqua solution = 0.2mm Indium at 20 degree Celsius |
| Melting Point | MnO2 - decomposes at 535 degree Celsius Zn = 420 degree Celsius, KOH aqua = -35 degree Celsius |
| Vapor Density (Air -1) | N/A |
| Evaporation Rate (Butyl Acetate = 1) | N/A |
| Solubility in Water | KOH – complete |

Appearance and Color

MnO2 is a black powder, Graphite is also a black powder, Zinc is a silver metal.

KOH aqua is a colorless liquid with stimulated odor.



Material Safety Data Sheet

4. First Aid Measures

In case of skin contact with content of battery, flush immediately with water. For eye contact, flush with copious amount of water for 10 minutes. If irritation persists, get medical help.

5. Fire Fighting Measures

| | |
|------------------------------------|----------------|
| Flash point (Method used) | Incombustible |
| Flammable Limits LBL UEL | Not Applicable |
| Extinguishing Media | -DO- |
| Special Fire Fighting Procedure | -DO- |
| Unusual Fire and Explosion Hazards | -DO- |

6. Accidental Release Measures

Route(s) of entry

| | |
|-------------|-----|
| Inhalation: | YES |
| Skin: | YES |
| Ingestion: | YES |

Health Hazards (Acute and Chronic)

These chemicals are contained in a sealed can. Risk of exposure occurs, only if battery is mechanically or electrically abused. The most likely risk is acute exposure when a cell vents KOH is caustic alkali and attack the skin and eyes. Contact of electrolyte with skin and eyes should be avoided.

| | |
|---------------------|------|
| Cardnogenicity NTP: | None |
| IARC Monographs: | None |
| OSHA Regulated: | None |

Signs and Symptoms of exposure

KOH can cause chemical burn upon contact with skin.

Medical Conditions

Generally aggravated by exposure.

An acute exposure will not generally aggravate any medical help.

Emergency and First Aid Procedures

In case of skin contact with content of battery, flush immediately with water. For eye contact, flush with copious amount of water for 10 minutes. If irritation persists, get medical help.



Material Safety Data Sheet

7. Handling and Storage

Steps to be taken in case material is released or spilled

Wipe out by wet duster

Waste Disposal Method

General abandonment

Precautions to be taken in handling and storing

Avoid mechanical or electrical abuse.

Other precautions

Do not short circuit, charge or dispose of in fire. Battery may explode or leak.

8. Exposure Controls/Personal Protection

| | |
|------------------------------------|---------------|
| Flash point (Method used) | Incombustible |
| Flammable Limits LBL UEL | N/A |
| Extngushing Media | N/A |
| Special Fire Figting Procedure | N/A |
| Unusual Fire and Explosion Hazards | N/A |

9. Physical and Chemical Properties

Compiled with 98/101/EEC & 91/157/EEC Specification (%)

| | |
|--------------------|----------|
| 1) Mercury Content | < 0.0001 |
| 2) Cadmium Content | < 0.001 |
| 3) Lead Content | < 0.001 |

10. Stability and Reactivity

| | |
|---------------------------------------|--|
| Stability | stable |
| Conditions to avoid | do not short-circuit, charge or dispose of in fire |
| Incompatibility (Materials to Avoid) | N/A |
| Hazardous polymerization | will not occur |
| Hazardous Decomposition or byproducts | N/A |



Material Safety Data Sheet

11. Toxicological Information

Route(s) of entry:

Inhalation: YES

Skin: YES

Ingestion: YES

Health Hazards (Acute and Chronic)

These chemicals are contained in a sealed can. Risk of exposure occurs, only if battery is mechanically or electrically abused. The most likely risk is acute exposure when a cell vents KOH is caustic alkali and attack the skin and eyes.

Contact of electrolyte with skin and eyes should be avoided.

Carinogenicity NTP: None

IARC Monographs: None

OSHA Regulated: None

Signs and Symptoms of exposure

KOH can cause chemical burn upon contact with skin.

Medical Conditions

Generally aggravated by exposure.

An acute exposure will not generally aggravate any medical help.

Emergency and First Aid Procedures

In case of skin contact with content of battery, flush immediately with water. For eye contact, flush with copious amount of water for 10 minutes. If irritation persists, get medical help.

12. Disposal Condition

Waste Disposal Method: General abandonment.



Material Safety Data Sheet

13. Regulatory Information

- Battery should be kept away from the reach of children.
- If the battery is accidentally swallowed, s/he should consult the doctor immediately.
- If the battery is used in the applications for children, the battery compartment should be capable of bombardment.
- If the applications have alternate power supply, the integrated circuit can only use primary battery instead of secondary battery.
- The battery should be placed correctly for the positive and negative terminals.
- Please do not try to heat, recharge or use other mean to recycle the primary battery.
- Please do not heat or throw the battery in fire or try to dismantle the battery by yourself.
- Please do not short circuit the battery.
- Please do not use electrical welding to weld the positive and negative terminals of battery directly.
- After the use of applications, please switch off the power supply.
- If the applications will not be used for a long period of time, the battery should be removed.
- Please change all the batteries at the same time instead of changing some of them only. Newly added batteries should not be mixed with the used ones as they have different chemical systems, grade and brand, etc. Otherwise, some batteries may be subject to leakage due to the extreme use.

14. Other Information

Products are according to IEC60086-2000 and 98/101/EC standard.

Do not short circuit, charge or dispose of in fire. Battery may explode or leak.

15. Transportation

We further declare the battery terminals are protect and the cargo is in all respects in proper condition for transport.

Alkaline batteries are considered to be „dry cell“ batteries and are not subject to dangerous goods regulation for the purpose of transportation by the International Civil Aviation Organization (ICAO), the International Air Transport Association (IATA) or the International Maritime Dangerous Goods regulations (IMDG). Alkaline batteries offered for transport are not subject to other provisions of these Regulations if they meet the following : „Cells and batteries are separated so as to prevent short circuits and are packed in strong packaging.“

„Referring the captioned shipment of battery, such battery have been packed in inner packing in such a manner as to effectively prevent from short circuits and the movements which could lead to short circuits.“

16. Other Information

Steps to be taken in case material is released or spilled:

Wipe out by wet duster. Avoid mechanical or electrical abuse.