

Date : 12.10.2010 Rev : PB-ST-1005

1. Chemical Product

MSDS Name: Camelion Alkaline Battery

Manufacturer: Camelion Enterprise Limited

Address:Ginza Square, No.565-567 Nathan Road, Kowloon, Hong Kong Tel: 0852 29549352 Fax: 0852 29542213

2. Composition /Information on Ingredients:

Chemical Nature: Alkaline Manganese Dioxide

CAS-No/EINECS NO.: Graphite (CAS# 7782-42-5)

POTASSIUM HYDROXIDE(CAS# 1310-58-3)

MANGANESE DIOXIDE (CAS# 1313-13-9)

ZINC(CAS# 7440-66-6)

Dangerous ingredients which have to be mentioned acc. To 99/45/EEC and it adaptations

Component	Content(%wt)	Appearance	Odor	Corrosion	Toxicity	Flammability
Zinc	18.0	Metal Can	None	None	None	None
Manganese	45.0	Black-brown	None			
Dioxide		Powder				
Carbon	2.5~3.5	Black Solid	None	None		
Rod						
Potassium	9.0~12.5	White solid	None	Strong		
Hydroxide				Corrosion		
Steel	18.0	Metal Solid	None	None	None	None
Brass	1.0	Plate	None	None	None	None
Plastic	2.0	Solid	None			
Mercury	<1ppm	Atom State	None			None
Cadmium	<10ppm	Atom State	None			None
Lead	<20ppm	Atom State	None			None

3. Hazards identifications

General

The battery should not be opened or discarded in fire or recharged or used improperly, or it could exposure. The ingredient and their combustion could be harmful.

Material or Ingredient	PEL (OSHA)	TLV (ACGIH)
Graphite	15.0mg/m ³ TWA (total dust)	2.0mg/m ³ TWA (respirable



Date : 12.10.2010 Rev : PB-ST-1005

	5.0mg/m ³ TWA (respirable	fraction)	
	fraction)		
Potassium Hydroxide	None established	2.0mg/m ³ CEILING	
Manganese Dioxide	5.0mg/m ³ CEILING (as Mn)	0.2mg/m ³ TWA (as Mn)	
	15.0mg/m ³ TWA (Total dust as	10.0mg/m ³ TWA (Inhalable	
	particulates not otherwise	particulate)	
Zinc	regulated)	3.0mg/m ³ TWA (Respirable	
ZIIIC	5.0mg/m ³ TWA (Respirable	particulate)	
	fraction as particulates not		
	otherwise regulated)		

	The Common known rules for handing of chemicals should		
Physical-Chemical Hazards:	be obeyed. Do not eat drink the product. This preparation is not classified as dangerous according		
Filysical-Chemical Hazalus.	to the criteria of directive 99/45/EEC		
Hazards to man:	This is preparation is classified Xi, N R38-43 according to		
	the CE directive , May cause sensitization by skin contract		
Hazards to environment:	When spilled, this product may raze the surface of plastic,		
	leather and paint, underground and surface water.		
4. First –aid measures:			
Inhalation:	In case of excessive inhalation remove the person to		
	fresh air and at rest Obtain medical advice.		
Skin Contact:	Remove contaminated clothing. Wash affected areas with		
	plenty of water and soap. If irritation occurs, consult a physician.		
Eye contact:	Rinse eyes immediately with running water for at least ten		
	minutes. Consult an ophthalmologist.		
Ingestion:	Rinse mouth with water. Give plenty of water to drink. Do		
	not induce vomiting. Obtain medical advice.		
5. Fire-fighting measures			
Suitable extinguishing media: powder.	Carbon dioxide (CO2), foam, dry chemical		
Extinguishing media not to be	used: Never use a direct water jet.		
Exposure hazards from comb	ustion products: In case of fire, carbon dioxide, carbon		
monoxide			
	and other toxic organic substances will be generated. Do not inhale fumes and smoke.		
Personal protective equipme	ents: Wear full protective clothing. Use self contained breathing apparatus.		
Remark:	Because of only keep about 10ml auto		

Camelion ® MATERIAL SAFETY DATA SHEET

According the European directive 2001/58/CE

Date : 12.10.2010 Rev : PB-ST-1005

perfume in care. Even if fire, It ca be extinguished by car extinguisher.

6. Accidental release measure Personal precautions persons away. Environmental precautions: Methods for cleaning up:	Wear protective clothing. Keep unprotected Avoid discharge and penetration into sewerage systems, waterways, pits, and cellars. Collect spilled material with an insert standard absorbent like sand or silica. Care for well-Ventilated conditions. Recycle or dispose of the materials in an appropriate way.
7. Handling and storage	
General	Obey the common known rules and precautions for handling with chemicals.
Fire/Explosion protection	Product vapors and oxygen/air may lead to potentially explosive mixtures. Keep ignition sources away. Do not smoke. Avoid electrostatic charge. Provide fire extinguisher.
Handling:	Accidental short circuit for a few seconds will not seriously affect the battery. But prolonged short circuit will cause the battery to lose energy, and can cause the safety release vent to open. Sources of short circuit include jumbled batteries in bulk containers, metal jewelry, metal covered tables or metal belts used for assembly of batteries in devices.
Charging:	This battery is not designed for recharging. Recharging can cause battery leakage or high pressure rupture, in some cases. Inadvertent charging can happen if a battery is installed backwards.
Storage:	Store product in well-filled, appropriate coated and tightly closed containers avoiding influence of oxygen/air, light and humidity .Store at a cool and constant temperature.
Disposal:	Dispose in accordance with all applicable federal, state,



Date : 12.10.2010 Rev : PB-ST-1005

and local regulations. Appropriate disposal technologies

include incineration and landfill.

8. Exposure controls/Personal protection

Exposition/ Technical measures Atmospheric vapor concentrations must be minimized by adequate ventilation.

Protection of hands, eyes and skin: To protect hands, eyes and skin, the use of appropriate chemical resistant glovers, safety glasses and suitable protective clothing is strictly recommended.

9. Physical and chemical propertied

Physical state	Liquid	Solubility in water	soluble
Color	Any colors	Vapor pressure	no applicable
Odor CC	OL COLOGNE Smell	Explosion limit	not applicable
pH value	not determined	Oxidizing properties	not applicable
Specific gravity	0.990-1.040 (at 25oC)	Flashpoint	not determined
Refractive index	1.480-1.515 (at 20oC)	Auto flammability	not determined
Solubility in ethan	ol soluble	Partition coefficient	not determined
Melting Point	not applicable	Boiling Point	not determined
Freezing Point	not determined		

10. Stability and Reactivity

Good stability at standard temperature. Avoid temperatures above or close to the flash point. Never heat sealed containers. This product presents no significant reactivity hazard, by itself or in contact water.

Reactivity: Avoid contact with acids. Alkali or strong oxidizing agents.

Hazardous decomposition products: carbon monoxide and unidentified organic compounds my be formed during combustion.

11. Toxicological information

The product is multi component mixture for which no toxicological date exists. This preparation is classified XI, N R38-43.

12. Ecological information

In general, no ecological date is available for preparations. Precautions Avoid disposing into drainage systems and in the environment.

13.Disposable considerations

Don not dispose of into environment or into sewerage. If recycling is not possible, the product and its container have to be disposed of in accordance with your local legislation and regulations. Alkaline batteries, containing corrosive electrolyte which will not flow out of the battery if the battery case is cracked are not subject to the provisions of this Code



Date : 12.10.2010 Rev : PB-ST-1005

provided the batteries are securely packed and protected against short-circuits.

14. Transport Information

Must have the strong packaging to prevent short circuit

This production is not hazardous under the applicable dot icao/iata, or IMDG regulation.

Alkaline batteries comply with Special Provisions A123 under the IATA.

Non-Hazardous for Sea Transport: Non-hazardous for sea transport.

The Internation Maritime Dangerous Goods Code (IMDG) regulate them for ocean transportation under Special Provision 304..

15.Regulatory Information

Symbol: N/A

Contains: Expiration date is on the battery bottom.

R/S-Phrases:

- R38 Irritation to skin
- R43 May cause sensitization by skin contact
- S2 Keep out of reach of children
- S24 Avoid contact with skin
- S37 Wear suitable gloves
- S61 Avoid release to environment. Refer to special instructions.

16.Other information

The information on this Material Safety Date Sheet (MSDS) was obtained form current and reputable sources. However, the data is provided without any warranty; expressed or implied, regarding its correctness or accuracy. It is the user's responsibility to assume liability on loss, injury, damage, or expense resulting from improper use of this product. Any previous MSDS of this product mentioned above are hereby replaced with this new document. We urge you to make this information available as appropriate in your organization and to any others with whom you arrange to handle this product.

Since the materials in this battery are sealed in the can, the potential for exposure to the components of the battery is negligible, when the battery is used as directed however, technical or electrical abuse of the battery may result in the release of battery contents.