

Phono jack, gold plated contacts, color coding


\*: 0-Black, 2-Red, 4-Yellow, 5-Green, 6-Blue, 9-White




Technical Information hide	
Product	
Title	NYS367-*
Title	11530/-
Electrical	
Dielectric strength	0.5 kVdc
Insulation resistance	≥ 1 GΩ
Rated current	depends on mated connector
Contact resistance	depends on mated connector
Mechanical	
Lifetime	> 1000 mating cycles
Panel thickness	max. 3 mm
Material	
Insulation	Thermoplastic
Environmental	
Temperature range	-25 °C to +70 °C

Data subject to change without prior notice. © 2012 NEUTRIK AG ® ALL RIGHTS RESERVED















## Content

Page

TINY xlr Cable Connectors 4
TINY xlr Chassis Connectors and Adapters
1/4'' Vertical Jacks 8
1/4'' Phone Jacks 10
1/4'' Phone Plugs 12
3.5 mm Phone Plugs, Cable Jacks and Adapter 14
Phono "RCA"16
DIN Connectors
Patch Box & Stage Boxes20
Dual Banana Plugs22





### REAN

With the brand REAN, the world's leading supplier of professional audio and video connectors – Neutrik AG – offers another interesting product range.


Excellent cost-performance ratio, attractive design and reliable functionality are the strengths of REAN.

Based on long-time know-how audio and video connectors for professional applications are developed and produced on up to date production facilities. An efficient logistics system and a global sales network make a high availability and short delivery times possible. The REAN product range is an alternative solution for cost sensitive applications.

REAN a brand of Neutrik AG







REAN 3

## N







### **TINY xlr Cable Connectors**







RT4FCT-B RT3MC-B

- 3, 4 and 5 pole versions available
- Easy to assemble
- Robust metal housing with best flex relief
- Shielded system high noise immunity and EMI protection
- Intuitive and rugged locking mechanism provides secure locking system
- Millionfold proven chuck type strain relief up to 4.00 mm cable diameter

### RT3FC-B



#### RT3FC-B-W




### Female Pin-Layouts (front view)






- Keyed insert and strain relief to avoid mispositioning/ rotation of insert respectively cable
- RT\*FC-B-W: optional sealing boot (patent pending) for water/sweat protection if mated with RT\*MP
- RT\*FCT-B: screw locking design for outstanding ruggedness – fits with common rear mountable connectors
- BRT-L: Accessory kit for cables from 4.00 5.00 mm


### RT3FCT-B



### RT3MC-B



### Male Pin-Layouts (front view)





## Ordering Information

Type No.		Description
Cable conne	ctors	
Female	Male	
RT3FC-B	RT3MC-B	3 pole TINY cable connector, black metal shell, gold plated contacts
RT4FC-B	RT4MC-B	4 pole TINY cable connector, black metal shell, gold plated contacts
RT5FC-B	RT5MC-B	5 pole TINY cable connector, black metal shell, gold plated contacts
RT*FC-B-D	RT*MC-B-D	TINY cable connector, black metal shell, gold plated contacts; bulk packed, to be ordered in multiples of 100 pcs.

Cable connectors female water resistant		
RT3FC-B-W	3 pole TINY female cable connector, black metal shell, water resistant boot, gold plated contacts	
RT4FC-B-W	4 pole TINY female cable connector, black metal shell, water resistant boot, gold plated contacts	
RT5FC-B-W	5 pole TINY female cable connector, black metal shell, water resistant boot, gold plated contacts	
RT*FC-B-W-D	TINY female cable connector, black metal shell, water resistant boot, gold plated contacts; bulk packed,	
	to be ordered in multiples of 100 pcs.	

Cable connectors female screw locking	
RT3FCT-B	3 pole TINY female cable connector with screw locking, black metal shell & nut, gold plated contacts
RT4FCT-B	4 pole TINY female cable connector with screw locking, black metal shell & nut, gold plated contacts
RT5FCT-B	5 pole TINY female cable connector with screw locking, black metal shell & nut, gold plated contacts
RT*FCT-B-D	TINY female cable connector with screw locking, black metal shell & nut, gold plated contacts; bulk packed,
	to be ordered in multiples of 100 pcs.

Accessories	
BRT-L	Bushing and chuck for cable diameters 4.0 - 5.0 mm

Specification	Cable connectors RT*FC-B*/RT*MC-B*	Screw locking RT*FCT-B*
Electrical		
Rated current per contact	< 5 A	< 5 A
Contact resistance	< 5 mΩ	< 5 mΩ
Insulation resistance	> 1 GΩ	> 1 GΩ
Dielectric strength	> 500 V rms	> 500 V rms
Mechanical		

Mechanica		
Lifetime	> 1'000 mating cycles	> 1'000 mating cycles
Cable O.D. range	2.0 - 4.0 mm	2.0 - 4.0 mm
Wiring	solder contacts	solder contacts
Max. wire size	0.22 mm² / 24 AWG	0.22 mm² / 24 AWG

Material		
Bushing	ABS	ABS
Contacts	female CuSn6 / male CuZn39Pb3	CuSn6
Contact plating	Au plated	Au plated
Insert	PA 6 30% GR	PA 6 30% GR
Shell (housing)	ZnAl4Cu1	ZnAl4Cu1
Shell plating	black	black
Strain relief	PVC	PVC
Protection boot	EPDM	-
Locking nut	-	Al, black anodized
Environment		
Operating temperature	-30°C to +85°C	-30°C to +85°C
Solderability	complies with IEC68-2-20	complies with IEC68-2-20

## Ν





**TINY xlr Chassis Connectors** 





## **TINY xlr Adapters**





**RT3MP** 

RT4MPR

- Front and rear mountable receptacles in 3, 4 and 5 pole design
- Watertight chassis connector, even in unmated condition
- RT\*MP provides water resistant connection if mated with RT\*FC-B-W





RA3FT-B

RA3MT-B

- Easy and fast solution to interconnect mini XLRs
- Rugged metal housing
- Mini XLR 3 pin to XLR-Male or XLR-Female

### **RT3MP**






### Panel Cutout




### Male Pin-Layouts (front view)






### RA3FT-B



RA3MT-B





## TINY xir

## Ordering Information

Type No.	Description
Chassis connectors	
RT3MP	3 pole TINY male chassis connector, nickel metal housing, gold plated contacts, max. panel thickness: 6 mm
RT4MP	4 pole TINY male chassis connector, nickel metal housing, gold plated contacts, max. panel thickness: 6 mm
RT5MP	5 pole TINY male chassis connector, nickel metal housing, gold plated contacts, max. panel thickness: 6 mm
RT*MP-D	TINY male chassis connector, nickel metal housing, gold plated contacts, max. panel thickness: 6 mm; bulk packed,
	to be ordered in multiples of 100 pcs.

Chassis connectors rearmountable		
RT3MPR	3 pole TINY rearmountable, male chassis connector, nickel metal housing, gold plated contacts, max. panel thickness: 3 mm	
RT4MPR	4 pole TINY rearmountable, male chassis connector, nickel metal housing, gold plated contacts, max. panel thickness: 3 mm	
RT5MPR	5 pole TINY rearmountable, male chassis connector, nickel metal housing, gold plated contacts, max. panel thickness: 3 mm	
RT*MPR-D	TINY rearmountable male chassis connector, nickel metal housing, gold plated contacts, max. panel thickness: 3 mm;	
	bulk packed, to be ordered in multiples of 100 pcs.	

Adapters	
RA3FT-B	3 pole adapter TINY male to female XLR, black metall shell, gold plated contacts
RA3MT-B	3 pole adapter TINY male to male XLR, black metall shell, gold plated contacts

Specification	Chassis connectors RT*MP*	Adapters RA*T-B	
Electrical			
Rated current per contact	< 5 A	-	
Contact resistance	< 5 mΩ	$\leq$ 5 m $\Omega$	
Insulation resistance	> 1 GΩ	> 1 GΩ	
Dielectric strength	> 500 V rms	500 V rms	
Mechanical			
Lifetime	> 1'000 mating cycles	> 1'000 mating cycles	
Wiring	solder contacts	_	
Max. wire size	0.22 mm² / 24 AWG	-	
Material			
Contacts	CuZn39Pb3	female CuSn6 / male CuZn39Pb3	
Contact plating	Au plated	Au plated	
Insert	PA 6 30% GR	PA 6 30% GR	
Shell (housing)	ZnAl4Cu1	ZnAl4Cu1	
Shell plating	nickel	black	
Environment			
Operating temperature	-30°C to +85°C	-20°C to +65°C	
Solderability	complies with IEC68-2-20	-	



## 1 / 4 " Vertical Jacks







**RJ3VM** 

RJ5VM


- Vertical PCB-mount Fit's widely used PCB layout of existing vertical jacks
- Space saving 1/4" jack enables highest packing density
- Circumferential contact arrangement provides reliable switching function
- Integrated body stop for the inserted 1/4" plug ensures best conductivity independent from mating tip shape
- Spring loaded ground contact maintains superior contact integrity








RJ5VM





## Ordering Information

Type No.	Description
1/4" Vertical Jack (bu	Ik packed, to be ordered in multiples of 100 pcs.)
RJ3VM	1/4" TRS Jack, vertical PCB, plastic housing, metal washer and nut, no normalling contacts
RJ5VM	1/4" TRS Jack, vertical PCB, plastic housing, metal washer and nut, with tip and ring normalling contacts

## Specification

Electrical	
Rated current per contact	3 A
Contact resistance	< 10 mΩ
Insulation resistance	$\geq$ 1 G $\Omega$
Dielectric strength	500 V dc

Mechanical				
Lifetime	> 1'000 mating cycles			
Insertion / withdrawal force	≤ 20 N / ≥ 10 N			

Material	
Contacts	CuSn6
Contact plating	Ag
Shell (housing)	PA6 30% GR
Thread nose	ZnAl4Cu1

Environment	
Operating temperature	-20°C to +70°C
Solderability	complies with IEC68-2-20









### 1/4" Phone Jacks





NYS 216 Horizontal Jack


NYS 2202 Long Bushing




NYS 230 Open Jack

- Robust and reliable jacks in metal or plastic housing
- Horizontal and vertical PCB-mount
- Extra long-threaded bushing for thick panel and guitar bodies
- Plastic nut or chrome ferrule nut
- Kinked solder pins secure jack to PCB







NYS 230




### NYS 221









A			and the second second
()ro	erind	Intor	mation
	i C i i i i g		mation

Type No.	Mono 2 pole	Stereo 3 pole	Description	Distance to PCB
1/4" long bu	shing jacks			
NYS 2202	•		Jack for thick panels, long-threaded bushing with washer and nut, full metal	-
NYS 2203		•	Jack for thick panels, long-threaded bushing with washer and nut, full metal	-
NYS 221		•	Jack with special design head for guitar strap, for thick panels,	-
			long-threaded bushing with washer and nut, full metal	

1/4" horizontal jacks (all contacts switch	ed)	
NYS 212 •	Plastic housing with washer and nut, solder tap version	-
NYS 2122 •	Plastic housing with washer and nut, solder tap version	-
NYS 215 •	With chrome ferrule nut	8.2 mm
NYS 2152 •	With chrome ferrule nut	8.2 mm
NYS 2152G •	With chrome ferrule nut and gold contacts	8.2 mm
NYS 2152G-DI-U •	Solder tap version with chrome ferrule nut, gold contacts, bulk packaging	-
NYS 216 •	Plastic housing with washer and nut	8.2 mm
NYS 2162 •	Plastic housing with washer and nut	8.2 mm
NYS 216G •	With gold contact	8.2 mm
NYS 218 •	With extra long contacts	15.0 mm
NYS 2182 •	With extra long contacts	15.0 mm
NYS 219 •	With long contacts	12.5 mm
NYS 2192 •	With long contacts	12.5 mm
A 7 A 10		
1/4" open jacks		
NYS 229 •	2 contacts, with washer and nut, panel thickness 3.5 mm	-
NYS 229L •	2 contacts, with longer threaded nose, washer and nut,	-
	panel thickness 6.5 mm, with 0.205" faston tabs	
NYS 230 •	3 contacts, with washer and nut, panel thickness 3.5 mm	-
1/4" vertical jacks		
NYS 232 •	Plastic housing, metal washer and nut, with tip and ring normalling contacts	24.85 mm

Specification	Phone jacks	
Electrical		
Rated current	depends on mating connector	
Contact resistance	depends on mating connector	
Insulation resistance	$\geq$ 1 G $\Omega$	
Dielectric strength	500 V dc	
Mechanical		
Lifetime	> 1`000 mating cycles	
Insertion/withdrawal force	≤ 20 N / ≥ 10 N	
Solderability	complies with IEC68-2-20	
Operating temperature	-20°C to +70°C	
Material		
Housing/handle	Brass Ni / Thermoplastic	
Insulation	Thermoplastic	
Contacts	Brass, SnCe / Au plated	

**REAN** 11




### 1/4"Phone Plugs







- Commercial 1/4" plugs and adapters
- All connectors according to EIA RS-453 / IEC 60603-11
- Short and long metal handles
- Plastic handle with flexible strain relief
- Heavy duty cable clamp for best strain relief

- Available with nickel, gold and black plating
- Large cable outlet and solder tabs
- Right angle version
- "Silent switch" on plug finger helps eliminate "pop" during insertion and withdrawal




NYS 224





NYS 225



Part number coding:	B black handle	G gold plated contacts	AG all gold, gold plated contacts and shell	
	BG black handle, gold plated contacts	S silent switch	GT gold plated tip contact	



0	 		1 f		
	er	n d		rmat	lon
~	· · ·				

Type No.	Mono 2 pole	Stereo 3 pole	Description	Cable O.D.
1/4" plugs	short handle			
NYS 201	•		Short turned metal handle	6 mm
NYS 202		•	Short turned metal handle	6 mm
1/4" plugs	plastic handle			
NYS 203	•		Plastic handle with flexible strain relief	6 mm
NYS 204		•	Plastic handle with flexible strain relief	6 mm
1/4" plugs	right angle			
NYS 207	•		Metal housing, plastic bushing	6 mm
NYS 207-2	•		Metal housing, red cover & plastic bushing	6 mm
NYS 208		•	Metal housing, plastic bushing	6 mm
1/4" plugs	long handle			
NYS 224	•		Long polished diecast handle, no rivet	6 mm
NYS 224AG	•		With gold plated handle and contacts	6 mm
NYS 224BG	•		With black metal handle, gold plated contacts	6 mm
NYS 224G	•		With gold plated contacts	6 mm
NYS 224GT	•		With gold plated tip contact	6 mm
NYS 224L	•		With large cable outlet	8 mm
NYS 224S	•		With tip switched to ground if not inserted (silent)	6 mm
NYS 224C-*	•		Diecast handle with coloured coding ring & rubber flex relief	6 mm
NYS 228		•	Stereo version of NYS 224	6 mm
NYS 228BG		•	With black metal handle, gold plated contacts	6 mm
NIVE 220C		•	With gold plated contacts	6 mm
NYS 228G				

1/4" plugs with large shell for speaker cables				
NYS 225	•	Large metal handle, rubber bushing	8 mm	
NYS 225B	•	With black metal handle	8 mm	
NYS 225L	•	With large cable outlet	9 mm	
NYS 2255	•	With tip switched to ground if not inserted (silent)	8 mm	

Specification		Phone plugs
Electrical		
Rated current and contact resistance		depends on mating connector
Insulation resistance		$\ge$ 1 G $\Omega$
Dielectric strength		500 V dc
Mechanical		
Lifetime		1`000 mating cycles
Solderability		complies with IEC68-2-20
Operating temperature		-20°C to +70°C
Material		
Housing/handle	Zinc Diecast, Ni / Au / black plated	• (NYS 203 / 204 ABS)
Insulation		Thermoplastic
Contacts		Brass, Ni / Au plated
Strain relief		Crimp type SnCe plated









Cable Jacks & Adapters



### 3.5 mm Phone Plugs





NYS 226

NYS 231BG





NYS 2202P Cable jack

NYS 240 Cable jack


NYS 236 Phone jack adapter

- Commercial 3.5 mm plugs
- All connectors according to EIA RS-453 / IEC 60603-11
- Heavy duty cable clamp for best strain relief
- Available with nickel and black plating
- Large cable outlet available




- Heavy duty cable clamp
- Available with nickel and black plating
- 1/4" adapters to interconnect mono & stereo lines


### NYS 231




### NYS 237



### NYS 2202P



### NYS 240





## Ordering Information

Type No.	Mono 2 pole	Stereo 3 pole	Description	Cable O.D.		
1/4" plug &	1/4" plug & jack adapters					
NYS 237	•		Mono plug adapter to mate standard 1/4" jacks, full metal	-		
NYS 239		•	Stereo plug adapter to mate standard 1/4" jacks, full metal	-		
NYS 236	•		Mono jack adapter to mate standard 1/4" plugs, full metal	-		
NYS 238		•	Stereo jack adapter to mate standard 1/4" plugs, full metal	_		
3.5 mm plug	S					
NYS 226	•		Metal handle with crimp strain relief	4 mm		
NYS 226B	•		With black metal handle	4 mm		
NYS 226BG	•		With black metal handle, gold plated contacts	4 mm		
NYS 226G	•		With gold plated contacts	4 mm		
NYS 226L	•		With large cable outlet	6 mm		
NYS 227		•	3.5 mm plug to 1/4" stereo jack adapter, all metal	-		
NYS 231		•	Metal handle with crimp strain relief	4 mm		
NYS 231B		•	With black metal handle	4 mm		
NYS 231BG		•	With black metal handle, gold plated contacts	4 mm		
NYS 231G		•	With gold plated contacts	4 mm		
NYS 231L		•	With large cable outlet	6 mm		
NYS 231LBG		•	With large cable outlet, black metal handle, gold plated contacts	6 mm		
NYS 231LL		•	With x-large cable outlet	8 mm		
NYS 231BG-LL		•	With x-large cable outlet, black metal handle, gold plated contacts	8 mm		
Cable jacks						
NYS 2202P	•		1/4" mono cable jack with metal handle	6 mm		
NYS 2203P		•	1/4" stereo cable jack with metal handle	6 mm		
NYS 240		•	3.5 mm stereo cable jack with metal handle	4 mm		
NYS 240BG		•	With black metal handle, gold plated contacts	4 mm		
NYS 240L		•	With large cable outlet	6 mm		

Specification	Cable Jacks & 3.5 mm plugs	Adapters
Electrical		
Rated current	depends on mating connector	depends on mating connector
Contact resistance	depends on mating connector	depends on mating connector
Insulation resistance	$\geq$ 1 G $\Omega$	$\geq$ 1 G $\Omega$
Dielectric strength	500 V dc	500 V dc
Mechanical		
Lifetime	1`000 mating cycles	1`000 mating cycles
Solderability	complies with IEC68-2-20	complies with IEC68-2-20
Insertion/withdrawal force	≤ 20 N / ≥ 10 N	complies with IEC68-2-20
Operating temperature	-25°C to +70°C	-25°C to +70°C
Material		
Housing/handle - Zinc Diecast Ni/Au/black plated	3.5 mm plugs	•
- Brass, Ni/black plated	cable jacks	_
Insulation	Thermoplastic	Thermoplastic
Contacts	Brass, Ni / Au plated	Brass, Ni / Au plated
Strain relief	Crimp type SnCe plated	-
Part number coding: B black handle BG black handle, gold plated	G gold plated contacts I contacts S silent switch	AG all gold, gold plated contacts and shell GT gold plated tip contact





## Phono ("RCA/Cinch")





NYS 354





NYS 355


• Heavy duty phono plugs


NYS 352G

- All metal
- Cable O.D. up to 7.2 mm
- Cable clamp or chuck type strain relief (NYS373\*)
- Phono receptacle for PCB-mounting
- Phono to phono female adapter


NYS 352

NYS 354






NYS 355



NYS 373-\*



## Ordering Information

Туре No.	Description	Cable O.D.
Phono ("RCA/Cinch	n")	
NYS 352	Phono plug	7.2 mm
NYS 352AG	Phono plug, all gold plated	7.2 mm
NYS 352B	Phono plug with black metal handle	7.2 mm
NYS 352BG	Phono plug with gold plated contacts and black metal handle	7.2 mm
NYS 352G	Phono plug with gold plated contacts	7.2 mm
NYS 354	Phono receptacle, PCB-mount, max. panel thickness 1.2 mm	-
NYS 355	Phono to phono female adapter	-
NYS 367-*	Phono chassis mount socket, gold plated contacts, color coding	-
NYS 372P	Phono jack with nickel plated contacts and handle	7.2 mm
NYS 372P-BG	Phono jack with gold plated contacts and black plated handle	7.2 mm
NYS 373-*	Phono plug with gold plated contacts, black chromium shell, chuck type strain relief	3.5 – 6.1 mm
	*) 0 - black, 2 - red, 4 - yellow, 5 - green, 6 - blue, 9 - white	

Specification		Phono ("RCA/Cinch")
Electrical		
Rated current		depends on mating connector
Contact resistance		depends on mating connector
Insulation resistance		$\geq$ 1 G $\Omega$
Dielectric strength		500 V dc
Mechanical		
Lifetime		> 1`000 mating cycles
Solderability		complies with IEC68-2-20
Operating temperature	2	-25°C to +70°C
Material		
Housing/handle		Zinc diecast or Brass Ni / Au / black plated
Insulation		Thermoplastic
Contacts		Brass, Ni / Au plated
Strain relief	- Crimp type SnCe plated	•
	- Chuck tye (POM)	NYS 373
Part number coding:	B black handle G gold plated conta BG black handle, gold plated contacts S silent switch	cts AG all gold, gold plated contacts and shell GT gold plated tip contact











NYS 324

- Male cable connectors with rugged diecast shell
- Flexible bushing
- Gold or silver plated non-tarnishing contacts
- Heavy duty cable clamp
- Female receptacle, stamped housing
- Complete shielding with ground contact
- Nickel-plated shell

### NYS 321









## DIN Connectors

## Ordering Information

NYS 326 7 pole, with silver plated contacts

. . . . .

Type No.	Description	Cable O.D.
DIN male cable co	nnectors	
NYS 321	3 pole, with silver plated contacts	5.0 mm
NYS 321G	3 pole with gold plated contacts	5.0 mm
NYS 322	5 pole, with silver plated contacts	5.0 mm
NYS 322G	5 pole with gold plated contacts	5.0 mm
NYS 322AG	5 pole with gold plated shell and contacts	5.0 mm
NYS 323	7 pole, with silver plated contacts	5.0 mm
NYS 323G	7 pole, with gold plated contacts	5.0 mm
DIN female chassis connectors		
NYS 324	3 pole, with silver plated contacts	-
NYS 325	5 pole, with silver plated contacts	_

Specification	DIN connectors	
Electrical		
Rated current	depends on mating connector	
Contact resistance	depends on mating connector	
Insulation resistance	$\geq$ 1 G $\Omega$	
Dielectric strength	500 V dc	

Mechanical	
Lifetime	> 1'000 mating cycles
Cable O.D.	5 mm
Solderability	complies with IEC68-2-20
Operating temperature	-25°C to +70°C

Material		
Housing/handle	- Zinc diecast Ni/Au plated	•
	- Steel, Ni plated	NYS 324 / 325 / 326
Insulation		Thermoplastic
Contacts		Brass, Ni / Au plated
Strain relief		Crimp type Zn plated
Part number coding:	B black handle G gold plate   BG black handle, gold plated contacts S	









### **Patch Box**






Stage Boxes

NYS-SSR-8


- "The Easy Way to Link your Audio System"
- 1/4" Patch box with 8 send/return moduls (split print)
- Metal housing reliable and robust
- Easy to assemble, simple to use

- Modular system for individual size and configuration
- Designed to be in an individual combination of connectors for "IN" and "OUT" and length
- Easy to assemble
- 3 pole XLR IDC receptacles eliminate stripping and tinning of wires
- Luminescent, self-adhesive labels for connector identification
- Extremely price competitive

- 1	 1	-	




Туре А	L
NSB1A	132 (5.2')
NSB2A	252 (9.93')
NSB3A	372 (14.65')
NSB4A	491 (19.33')



	Type B
	NSB1B
	NSB2B
117 (4.6*)	NSB3B


Туре В	L
N S B 1 B	132 (5.2')
N S B 2 B	252 (9.93')
NSB3B	372 (14.65')

L



турес	L L
NSB1C	132 (5.2')
NSB2C	252 (9.93')
NSB3C	372 (14.65')

### NYS SSR-8



## Ordering Information

Patch box	
NYS-SSR-8	1/4" patch box with 8 send/return moduls (split print)

Stage boxes – type A	A
NSB1A-8/4	Length 1, 8 IN (female/send) and 4 OUT (male/return)
NSB2A-12/4	Length 2, 12 IN (female/send) and 4 OUT (male/return)
NSB2A-20/4	Length 2, 20 IN (female/send) and 4 OUT (male/return)
NSB3A-32/4	Length 3, 32 IN (female/send) and 4 OUT (male/return)
NSB4A-40/4	Lenght 4, 40 IN (female/send) and 4 OUT (male/return)
NSB4A-40/8	Lenght 4, 40 IN (female/send) and 8 OUT (male/return)

Stage boxes – type B		
NSB1B-8/0	Length 1, 8 IN (female/send)	
NSB2B-12/4	Length 2, 12 IN (female/send) and 4 OUT (male/return)	
NSB2B-16/0	Length 2, 16 IN (female/send)	
NSB3B-20/4	Length 3, 20 IN (female/send) and 4 OUT (male/return)	

Stage boxes – type C		
NSB1C-8/0	Length 1, 8 IN (female/send)	
NSB2C-12/4	4 Length 2, 12 IN (female/send) and 4 OUT (male/return)	
NSB3C-20/4	Length 3, 20 IN (female/send) and 4 OUT (male/return)	

(Supplied as disassembled set comprising of all hardware parts including plates, profiles, strain relief, endpieces and screws.)

Specification		1/4" patch box	Stage boxes	
Electrical				
Rated current	depends on mating connector	•	2 A	
Contact resistance	depends on mating connector	•	< 5 mΩ	
Insulation resistance		$\geq$ 1 G $\Omega$	$\geq$ 1 G $\Omega$	
Dielectric strength		500 V dc	500 V dc	
Mechanical				
Lifetime		> 10'000 mating cycles	> 1'000 mating cycles	
Insertion/withdrawal force		$\leq$ 10 N / $\geq$ 10 N	≤ 10 N / ≥ 10 N	
Multicore cable O.D.		-	15/20 mm	
Applicable wire size		_	0.22 mm <sup>2</sup> / 24 AWG and 0.14 mm <sup>2</sup> / 26 AWG	
Operating temperature		-25°C to + 70°C	-25°C to + 70°C	
Material				

Housing		Aluminium	Aluminium
Quad plates		-	POM
End pieces		Thermoplastic	Thermoplastic
Contacts	Brass/Bronze	Ni plated	Au plated
Part number coding:	B black handle BG black handle, gold plated contacts		AG all gold, gold plated contacts and shell GT gold plated tip contact





## Dual Banana Plugs






NYS 508-R

NYS 508-B

- Cable strain relief: teethed cable clamp featuring cable O.D. 6.0–10.5 mm
- Protection against electric shock: cable ends and plugs are completely covered in mated condition
- Gold plated contacts for tarnish resistance & long insertion life





# Dual Banana Plugs

Ordering Information				
Type No.	Description			Cable O.D.
Dual banana plugs				
NYS 508-R	Dual banana plug, red housing			6.0 – 10.5 mm
NYS 508-B	Dual banana plug, black housing			6.0 – 10.5 mm
Specification				Dual banana plug
Electrical				
Rated current				20 A
Insulation resistance				$\geq$ 1 G $\Omega$
Dielectric strength				500 V dc
Mechanical				
Lifetime				> 1`000 mating cycles
Operating temperature				-25°C to +50°C
Material				
Insulation				Thermoplastic
Contacts				Brass plated
Strain relief				Teethed cable clamp
Part number coding:	B black handle BG black handle, gold plated contacts	G gold plated co S silent switch		AG all gold, gold plated contacts and shell GT gold plated tip contact

Liechtenstein (Headquarters) NEUTRIK AG, Im alten Riet 143, 9494 Schaan T +423 237 24 24, F +423 232 53 93, neutrik@neutrik.com

### Germany/Netherlands/Denmark/Austria

Neutrik Vertriebs GmbH, Felix-Wankel-Strasse 1, 85221 Dachau, Germany T +49 8131 28 08 90, info@neutrik.de

#### **Great Britain**

Neutrik (UK) Ltd., Westridge Business Park, Cothey Way Ryde, Isle of Wight PO33 1 QT T +44 1983 811 441, sales@neutrik.co.uk

#### France

Neutrik France SARL, Rue du Parchamp 13, 92100 Boulogne-Billancourt T +33 1 41 31 67 50, info@neutrik.fr

#### USA

Neutrik USA Inc., 4115 Taggart Creek Road, Charlotte, North Carolina, 28208 T +1 704 972 30 50, info@neutrikusa.com

#### Japan

Neutrik Limited, Yusen-Higashinihonbashi-Ekimae Bldg., 3-7-19 Higashinihonbashi, Chuo-ku, Tokyo 103 T +81 3 3663 47 33, mail@neutrik.co.jp

#### Hong Kong

Neutrik Hong Kong LTD., Unit 18, 7 Floor Shatin Galleria Nr. 18-24 Shan Mei Street, Foatan, Shatin T +852 2687 6055, neutrik@neutrik.com.hk

#### China

Ningbo Neutrik Electronics Co., Ltd., Shiqi Street, Yinxian Road West Fengjia Villiage, Yinzhou Area, Ningbo, Zhejiang; 315153 T +86 574 88250488 800, neutrik@neutrik.com.cn

www.rean-connectors.com