



## ZMLF.E488001 Bare and Covered Ferrules

[Page Bottom](#)

### Bare and Covered Ferrules

[See General Information for Bare and Covered Ferrules](#)

PHOENIX CONTACT GMBH & CO KG

E488001

FLACHSMARKTSTRASSE 8

32825 BLOMBERG, GERMANY

Non-insulated ferrules, Cat. Nos. A 0.5-10, A 0.5-6, A 0.5-8, A 0.75-10, A 0.75-12, A 0.75-6, A 0.75-8, A 1.5 -18, A 1.5-10, A 1.5-12, A 1.5-15, A 1.5-20, A 1.5-7, A 1.5-8, A 10-12, A 10-15, A 10-18, A 10-20, A 10-25, A 1-10, A 1-12, A 1-6, A 16-12, A 16-15, A 16-18, A 16-20, A 16-25, A 16-32, A 1-7, A 1-8, A 2.5-10, A 2.5-12, A 2.5-15, A 2.5-18, A 2.5-20, A 2.5-7, A 2.5-8, A 25-12, A 25-15, A 25-18, A 25-25, A 25-32, A 35-18, A 35-20, A 35-25, A 35-32, A 4 -20, A 4-10, A 4-10, A 4-12, A 4-18, A 4-9, A 50-18, A 50-22, A 50-25, A 50-32, A 6-10, A 6-12, A 6-15, A 6-18, A 6-20.

Insulated ferrules, Cat. Nos. AI 0.5 - 10 OG, AI 0.5 - 6 OG, AI 0.5 - 6 WH, AI 0.5 - 8 OG, AI 0.5 - 8 WH, AI 0.5 -10 WH, AI 0.5 -12 OG, AI 0.5 -12 WH, AI 0.75- 6 BU, AI 0.75- 6 GY, AI 0.75- 6 WH, AI 0.75- 8 BU, AI 0.75- 8 GY, AI 0.75- 8 WH, AI 0.75-10 BU, AI 0.75-10 GY, AI 0.75-10 WH, AI 0.75-12 BU, AI 0.75-12 GY, AI 0.75-12 WH, AI 1 - 6 RD, AI 1 - 6 YE, AI 1 - 8 RD, AI 1 - 8 YE, AI 1 -10 RD, AI 1 -10 YE, AI 1 -12 RD, AI 1 -12 YE, AI 1.5 - 6 BK, AI 1.5 - 6 RD, AI 1.5 - 8 BK, AI 1.5 - 8 RD, AI 1.5 -10 BK, AI 1.5 -10 RD, AI 1.5 -12 BK, AI 1.5 -12 RD, AI 1.5 -18 BK, AI 1.5 -18 RD, AI 10 -12 BN, AI 10 -12 IV, AI 10 -12 RD, AI 10 -18 BN, AI 10 -18 IV, AI 10 -18 RD, AI 16 -12 BU, AI 16 -12 GN, AI 16 -12 WH, AI 16 -18 BU, AI 16 -18 GN, AI 16 -18 WH, AI 2 - 8 YE, AI 2.5 - 8 BU, AI 2.5 - 8 GY, AI 2.5 -10 BU, AI 2.5 -10 GY, AI 2.5 -12 BU, AI 2.5 -12 GY, AI 2.5 -18 BU, AI 2.5 -18 GY, AI 25 -16 BK, AI 25 -16 BN, AI 25 -16 YE, AI 25 -18 BK, AI 25 -18 BN, AI 25 -18 YE, AI 25 -22 BK, AI 25 -22 BN, AI 25 -22 YE, AI 35 -16 BE, AI 35 -16 RD, AI 35 -18 BE, AI 35 -18 RD, AI 35 -25 BE, AI 35 -25 RD, AI 4 -10 GY, AI 4 -10 OG, AI 4 -12 GY, AI 4 -12 OG, AI 4 -18 GY, AI 4 -18 OG, AI 50 -20 BU, AI 50 -20 OL, AI 50 -25 BU, AI 50 -25 OL, AI 6 -12 BK, AI 6 -12 GN, AI 6 -12 YE, AI 6 -18 BK, AI 6 -18 GN, AI 6 -18 YE, AI 0.5- 8 OG-GB, AI 0.5- 8 WH-GB, AI 0.5-10 OG-GB, AI 0.5-10 WH-GB, AI 0.75- 8 BU-GB, AI 0.75- 8 GY-GB, AI 0.75- 8 WH-GB, AI 0.75-10 BU-GB, AI 0.75-10 GY-GB, AI 0.75-10 WH-GB, AI 0.75-12 BU-GB, AI 0.75-12 GY-GB, AI 0.75-12 WH-GB, AI 1- 8 RD-GB, AI 1- 8 YE-GB, AI 1.5- 6 BK-GB, AI 1.5- 6 RD-GB, AI 1.5- 8 BK-GB, AI 1.5-10 BK-GB, AI 1.5-10 RD-GB, AI 1-10 RD-GB, AI 1-10 YE-GB, AI 1-12 RD-GB, AI 1-12 YE-GB, AI 16-12 BU-GB, AI 16-12 GN-GB, AI 16-12 WH-GB, AI 16-18 BU-GB, AI 16-18 GN-GB, AI 16-18 WH-GB, AI 2.5-10 BU-GB, AI 2.5-10 GY-GB, AI 2.5-12 BU-GB, AI 2.5-12 GY-GB, AI 2.5-8 BU-GB, AI 2.5-8 GY-GB, AI 4-10 GY-GB, AI 4-12 GY-GB, AI-XL 6 -12 YE, AI-XL 1.5 -10 BK, AI-XL 1.5 -8 BK, AI-XL 10 -12 RD, AI-XL 2.5 -12 BU, AI-XL 2.5-8 BU, AI-XL 4-10 GY, AI 0.5-8 OG-B, AI 0.5-8 WH-B, AI 0.75-8 BU-B, AI 0.75-8 GY-B, AI 0.75-8 WH-B, AI 1.5-8 BK-B, AI 1.5-8 RD-B, AI 1-8 RD-B, AI 1-8 YE-B, AI 2.5-8 BU-B, AI 2.5-8 GY-B.

Insulated twin ferrules, Cat. Nos. AI-TWIN 2X0.5-10 OG, AI-TWIN 2X0.5-10 WH, AI-TWIN 2X0.5-6 OG, AI-TWIN 2X0.5-6 WH, AI-TWIN 2X0.5-8 OG, AI-TWIN 2X0.5-8 WH, AI-TWIN 2X0.75-10 BU, AI-TWIN 2X0.75-10 GY, AI-TWIN 2X0.75-10 WH, AI-TWIN 2X0.75-12 BU, AI-TWIN 2X0.75-12 GY, AI-TWIN 2X0.75-12 WH, AI-TWIN 2X0.75-8 BU, AI-TWIN 2X0.75-8 GY, AI-TWIN 2X0.75-8 WH, AI-TWIN 2X1.5 -12 RD, AI-TWIN 2X1.5-12 BK, AI-TWIN 2X1.5-8 BK, AI-TWIN 2X1.5-8 RD, AI-TWIN 2x10-14 BN, AI-TWIN 2X10-14 IV, AI-TWIN 2X10-14 RD, AI-TWIN 2X1-10 RD, AI-TWIN 2X1-10 YE, AI-TWIN 2X1-12 RD, AI-TWIN 2X1-12 YE, AI-TWIN 2X16-16 BU, AI-TWIN 2X16-16 GN, AI-TWIN 2x16-16 WH, AI-TWIN 2X1-8 RD, AI-TWIN 2X1-8 YE, AI-TWIN 2X2.5-10 BU.

[Last Updated](#) on 2016-11-10

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2016 UL LLC

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2016 UL LLC".