

Ferrule - AI 0,25- 6 YE - 3203024

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Ferrule, Length: 10.5 mm, Color: yellow

The figure shows the version AI 1-8 YE

Product Features

- The AI 0,25.. ferrules can also be used to process 0.14 mm² conductors
- The ferrules with plastic sleeve are made from soft tin-plated electrolytic copper
- The insulation reliability of close connections is increased and the splicing of wires is prevented

Key commercial data

| | |
|------------------|---------------|
| package_quantity | 100 |
| GTIN | 4046356012973 |

Technical data

Dimensions

| | |
|--|---------|
| Length (b) | 10.5 mm |
| Sleeve length | 6 mm |
| Inner dimension of the insulating collar (d) | 2 mm |
| Ferrule diameter | 0.8 mm |
| Insulating collar thickness | 0.25 mm |
| Sleeve wall thickness | 0.15 mm |

Ambient conditions

| | |
|----------------------------|--------|
| Short-term temperature | 120 °C |
| Max. permanent temperature | 105 °C |

General

| | |
|---|--------------------------------|
| Color | yellow |
| Components | free from silicone and halogen |
| Inflammability class according to UL 94 | HB |
| Material | E-CU |

classifications

eCl@ss

Ferrule - Al 0,25- 6 YE - 3203024

classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27060701 |
| eCl@ss 4.1 | 27060701 |
| eCl@ss 5.0 | 27400201 |
| eCl@ss 5.1 | 27400201 |
| eCl@ss 6.0 | 27400201 |
| eCl@ss 7.0 | 27400201 |
| eCl@ss 8.0 | 27400201 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000005 |
| ETIM 3.0 | EC000005 |
| ETIM 4.0 | EC000005 |
| ETIM 5.0 | EC000005 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30212109 |
| UNSPSC 7.0901 | 27121703 |
| UNSPSC 11 | 27121703 |
| UNSPSC 12.01 | 27121703 |
| UNSPSC 13.2 | 27121703 |

approvals

CSA / CSAus / cCSAus /

Approval details

| | |
|---|--|
|  | |
| Nominal voltage UN | |
| Nominal current IN | |
| mm ² /AWG/kcmil | |

| | |
|----------------------------|--|
| CSAus | |
| Nominal voltage UN | |
| Nominal current IN | |
| mm ² /AWG/kcmil | |

| |
|---------------|
| cCSAus |
|---------------|

Ferrule - AI 0,25- 6 YE - 3203024

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>