




REACH&RoHS Compliant



CABLE LABEL1
 (Color of paper: white/text: black)

Part No.: ITEM NO
 Code 39: Shipment batch
 change with order
 S/N: WWYY
 Year(2017=17)
 Week




- NOTE:** CABLE MUST Print: E314459 见 AWM 20276 80°C 30V VW-1 HIGH SPEED HDMI CABLE WITH ETHERNET Assmann Electronic GmbH, 58513 Lüdenscheid, Germany
- CABLE: 28AWG(1/0.32BC),UL20276,AL/MY+B-FOIL,(#28*1P+D+AL)*4PCS+28AWG*1P+28AWG*5C OD=6.5±0.2mm,BLACK COLOR,PVC JACKET.
 - LENGTH: 10M.
 - CONNECTORS: P1&P2: HDMI(M)*2PCS(BLACK INSULATOR)(SHELL GOLD PLATED).
 - MOLD: MOLDING TYPE.
 - CONTACTS:

- NOTE:**
- Operating Temperature : <80°
 - Operating Humidity: <75%
 - Storage Temperature: <50°
 - Storage Humidity<65%

HDMI(M)(P1)	1	3	2	4	6	5	7	9	8	10	12	11	13	14	17	18	19	15	16	64
HDMI(M)(P2)	1	3	2	4	6	5	7	9	8	10	12	11	13	14	17	18	19	15	16	64
	PAIR		DRAIN		PAIR		DRAIN		PAIR		DRAIN		5C				PAIR		SHELL	

- Test machine test condition.
 - A.100% OPEN,SHORT&INTERMITANCE TEST.
 - B.CONDUCTOR RESISTANCE: 3ohms MAX:
 - C.INSULATION RESISTANCE: 5M Min/,10ms:
- ALL MUST BE MEET ON ROHS COMPLIANT.



	Date	Name	Part No.
Drawn by	2020.05.19	Yuwenming	AK-330105-100-S
Checked by	2020.05.19	Zhouwei	EAN:
Approved by			Title
ASSMANN Electronic GmbH			HDMI M/M
			Scale Unit
80496			Sheet 1/2