



**REACH&RoHS Compliant**




HDMI(M)  
(MOLDING BLACK COLOR)  
SOURCE TO HOST



Part No.: 客人料号  
Code 39: 随订单出货批次更改  
S/N: WWYY  
Year(2017=17)  
Week

**CABLE LABEL1**  
(Color of paper: white/text: black)




HDMI(M)  
(MOLDING RED COLOR)  
TV Terminal TO Display

- NOTE: CABLE MUST Print: E314459 见 AWM 20276 80°C 30V VW-1 HIGH SPEED HDMI<sup>®</sup> CABLE WITH ETHERNET Assmann Electronic GmbH, 58513 Lüdenscheid, Germany
- CABLE: 28AWG(1/0.32BC),UL20276,AL/MY+B-FOIL,(#28\*1P+D+AL)\*4PCS+28AWG\*1P+28AWG\*5C OD=6.5±0.2mm,BLACK COLOR,PVC JACKET.
  - LENGTH: 20M.
  - CONNECTORS: P1&P2: HDMI(M)\*2PCS(BLACK INSULATOR)(SHELL GOLD PLATED).
  - MOLD: MOLDING TYPE.
  - CONTACTS:

- NOTE:
- Operating Temperature : <80°
  - Operating Humidity: <75%
  - Storage Temperature: <50°
  - Storage Humidity<65%

HDMI(M)(P1)	1	3	2	4	6	5	7	9	8	10	12	11	13	14	17	18	19	15	16	64
HDMI(M)(P2)	1	3	2	4	6	5	7	9	8	10	12	11	13	14	17	18	19	15	16	64
	PAIR		DRAIN		PAIR		DRAIN		PAIR		DRAIN		5C					PAIR		SHELL

- Test machine test condition.
  - A.100% OPEN,SHORT&INTERMITANCE TEST.
  - B.CONDUCTOR RESISTANCE: 3ohms MAX:
  - C.INSULATION RESISTANCE: 5M Min/,10ms:
- ALL MUST BE MEET ON ROHS COMPLIANT.



	Date	Name	Part No.
Drawn by	2020.05.19	Yuwenming	AK-330105-200-S
Checked by	2020.05.19	Zhouwei	EAN:
Approved by			Title
ASSMANN Electronic GmbH			HDMI M/M
			Scale Unit
80496			Sheet 1/2