

Surge protection device - PT-IQ-4X1+F-24DC-PT - 2801272

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Surge protection, consisting of protective plug and base element, with integrated multi-stage status indicator on the module for four signal wires with common reference potential. Indirect grounding via gas-filled surge arrester.

The figure shows the PT-IQ-2x2-24DC-PT version



Key commercial data

package_quantity	1
GTIN	4046356766548

Technical data

Dimensions

Height	109.3 mm
Width	17.7 mm
Depth	77.5 mm
Pitch unit	1 Div.

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Degree of protection	IP20

General

Housing material	PA 6.6
Inflammability class according to UL 94	V0
Color	black
Mounting type	DIN rail mounting
Design	DIN rail module, two-section, divisible
Direction of action	Line-Line & Line-Signal Ground/Shield & optional Signal Ground/ Shield-Earth Ground

Protective circuit

IEC test classification	C1
IEC test classification	C2
IEC test classification	C3

Surge protection device - PT-IQ-4X1+F-24DC-PT - 2801272

Technical data

Protective circuit

IEC test classification	D1
Nominal voltage U_N	24 V DC
Maximum continuous operating voltage U_C	30 V DC
Maximum continuous operating voltage U_C	21 V AC
Nominal current I_N	700 mA (up to 50°C)
Operating effective current I_C at U_C	≤ 1 mA (per path)
Residual current I_{PE}	≤ 1 μ A
Nominal discharge current I_n (8/20) μ s (Core-Earth)	10 kA
Impulse discharge current (10/350) μ s, peak value I_{imp}	2.5 kA
Voltage protection level U_P (Core-Earth)	≤ 800 V (C1 - 1 kV/500 A)
Voltage protection level U_P (Core-Earth)	≤ 950 V (C2 - 10 kV / 5 kA)
Voltage protection level U_P (Core-Earth)	≤ 780 V (C3 - 25 A)
Voltage protection level U_P (Core-GND)	≤ 75 V (C1 - 1 kV/500 A)
Voltage protection level U_P (Core-GND)	≤ 135 V (C2 - 10 kV / 5 kA)
Voltage protection level U_P (Core-GND)	≤ 55 V (C3 - 25 A)
Voltage protection level U_P static (core-ground)	≤ 80 V (C2 - 10 kV / 5 kA)
Voltage protection level U_P static (core-ground)	≤ 75 V (C3 - 25 A)
Response time t_A (Core-Earth)	≤ 1 ns
Response time t_A (Core-Earth)	≤ 100 ns
Input attenuation aE, asym.	typ. 0.3 dB (≤ 300 kHz / 150 Ω)
Cut-off frequency f_g (3 dB), asym. (GND) in 150 Ohm system	typ. 1.1 MHz
Capacity (Core-GND)	typ. 2 nF
Resistance in series	1.2 $\Omega \pm 5$ %
Message: Surge protection fault	Optical, multi-stage
Max. required back-up fuse	0.8 A (FF)
Surge carrying capacity in acc. with IEC 61643-21 (Core-Earth)	D1 (2.5 kA)
Surge carrying capacity in acc. with IEC 61643-21 (Core-Earth)	C2 - 10 kA
Surge carrying capacity in acc. with IEC 61643-21 (Core-Earth)	C3 - 25 A
Surge carrying capacity in acc. with IEC 61643-21 (Core-GND)	C2 - 10 kA
Surge carrying capacity in acc. with IEC 61643-21 (Core-GND)	C3 - 25 A
Pulse reset time t_r in acc. with IEC 61643-21 (Core-Earth)	≤ 30 ms
Pulse reset time t_r in acc. with IEC 61643-21 (Core-GND)	≤ 350 ms
Overload failure mode as per IEC 61643-21 (plug)	Mode 2
Overload failure mode as per IEC 61643-21 (GND-Ground base element)	Mode 2

Connection data

Connection method	Push-in connection
Connection type IN	Push-in connection
Connection type OUT	Push-in connection
Stripping length	10 mm

Surge protection device - PT-IQ-4X1+F-24DC-PT - 2801272

Technical data

Connection data

Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section solid min.	0.5 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12

Connection, equipotential bonding

Connection method	NS 35 DIN rail or connection terminal block
-------------------	---

classifications

eCl@ss

eCl@ss 4.0	27140201
eCl@ss 4.1	27130801
eCl@ss 5.0	27130801
eCl@ss 5.1	27130801
eCl@ss 6.0	27130807
eCl@ss 7.0	27130807
eCl@ss 8.0	27130807

ETIM

ETIM 3.0	EC000943
ETIM 4.0	EC000943
ETIM 5.0	EC000943

UNSPSC

UNSPSC 6.01	30212010
UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610
UNSPSC 13.2	39121620

accessories

Marker pen

X-PEN 0,35 - 0811228



Surge protection device - PT-IQ-4X1+F-24DC-PT - 2801272

accessories

Terminal marking

ZBF 5:UNBEDRUCKT - 0808642



ZBF 5/WH-100:UNBEDRUCKT - 0808668



Labeled terminal marker

ZBF 5,LGS:FORTL.ZAHLEN - 0808671



ZBF 5,LGS:GERADE ZAHLEN - 0810821



ZBF 5,LGS:UNGERADE ZAHLEN - 0810863



Surge protection device - PT-IQ-4X1+F-24DC-PT - 2801272

accessories

ZBF 5,QR:FORTL.ZAHLEN - 0808697



Device marking

ZBN 18:UNBEDRUCKT - 2809128



Mounting material

E/ME TBUS NS35 GY - 2713780



PCB plug

FK-MC 0,5/ 5-ST-2,5 - 1881354



accessories

ZBF 15:SO/CMS - 0814717



Surge protection device - PT-IQ-4X1+F-24DC-PT - 2801272

accessories

ZBF 5:SO/CMS - 0808707




ZBN 18:SO/CMS - 0800763




Drawings

Application drawing




Surge protection device - PT-IQ-4X1+F-24DC-PT - 2801272

Diagram




Dimensioned drawing



Surge protection device - PT-IQ-4X1+F-24DC-PT - 2801272

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>