





# MODEL-MTS602



## MOUNTING HOLES



Tolerance: ±0.4

### \*\*Mechanical Specification

- Service life : 100,000 operations min.
- Operating Force (OF) : 120 ± 50 g.
- Releasing Force (RF) : Min. 20 g.
- Travel : 0.25 ± 0.1 mm.
- Free Position (FP) (L) : 5.1 ± 0.4 mm.
- Feeling : Tactile.
- Contact Style : Mechanical contact.
- Control strength : 1 kg static force.

### \*\*Electrical Specification

- Rating : 50mA 12 VDC.
- Contact Resistance : 100 m ohms max.
- Insulation Resistance : 100 M ohms min. (at 250 VDC)
- Service life : 100,000 min.
- Bounce : 10 m sec. max.

### \*\*Durability Specification

- Test condition : at a rate of 15 - 20 cycles for 1 minute, with a resistive load of DC 12V 50mA.
- Ambient Temperature : -15 °C to + 70 °C
- Ambient Humidity : 85% RH max.
- Bounce : 20m sec. max.
- Operating Force : within +10% to -10% of initial value.
- Solder Dip Time : within 1 sec. at 250 ± 5°C

W/BEST REBOARDS.