

## Relay connectors - ST-REL2-KG 24/1AU - 2823722

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Relay connector, equipped with miniature switching relay, contacts (AgPd60): small loads, 1 N/O contact, input voltage 24 V AC/DC, with light indicator, can be plugged on basic termination blocks

### Key commercial data

<b>package_quantity</b>	10
<b>GTIN</b>	4017918077549

### Technical data

#### Dimensions

<b>Width</b>	14.6 mm
<b>Height</b>	33 mm
<b>Depth</b>	66.5 mm

#### Ambient conditions

<b>Ambient temperature (operation)</b>	-20 °C ... 50 °C
<b>Ambient temperature (storage/transport)</b>	-20 °C ... 70 °C

#### Coil side

<b>Nominal input voltage <math>U_N</math></b>	24 V AC/DC
<b>Input voltage range in reference to <math>U_N</math></b>	0.8 ... 1.1
<b>Nominal input current at <math>U_{IN}</math></b>	21 mA
<b>Typical response time</b>	7 ms (with DC)
<b>Typical release time</b>	11 ms (with DC)
<b>Operating voltage display</b>	Yes
<b>Protective circuit</b>	Bridge rectifier, varistor

#### Contact side

<b>Contact type</b>	Double contact, 1 N/O contact
<b>Contact material</b>	AgPd60, hard gold-plated
<b>Maximum switching voltage</b>	30 V AC
<b>Maximum switching voltage</b>	36 V DC
<b>Maximum inrush current</b>	0.2 A
<b>Limiting continuous current</b>	0.5 A
<b>Interrupting rating (ohmic load) max.</b>	5 W (at 24 V DC)
<b>Note</b>	the following values are applicable if a gold layer is destroyed

## Relay connectors - ST-REL2-KG 24/1AU - 2823722

### Technical data

#### Contact side

Maximum switching voltage	125 V AC
Limiting continuous current	2 A
Maximum inrush current	2 A
Interrupting rating (ohmic load) max.	29 W (at 24 V DC)
Interrupting rating (ohmic load) max.	29 W (at 48 V DC)
Interrupting rating (ohmic load) max.	29 W (at 60 V DC)
Interrupting rating (ohmic load) max.	60 VA (for 250 V AC)

#### General

Test voltage relay winding/relay contact	2.5 kV AC (50 Hz, 1 min.)
Operating mode	100% operating factor
Mechanical service life	Approx. $2 \times 10^7$ cycles
Standards/regulations	DIN VDE 0110b, Gr. C for 250 V DC
Standards/regulations	IEC 60255/DIN VDE 0435 (in relevant parts)
Standards/regulations	DIN EN 50178/DIN VDE 0160 (in relevant parts)
Standards/regulations	EN 60730/DIN VDE 0631
Standards/regulations	DIN VDE 0160 (in relevant parts)

### classifications

#### eCl@ss

eCl@ss 4.0	27371104
eCl@ss 4.1	27371104
eCl@ss 5.0	27371001
eCl@ss 5.1	27371001
eCl@ss 6.0	27371001
eCl@ss 7.0	27371001
eCl@ss 8.0	27371001

#### ETIM

ETIM 2.0	EC000196
ETIM 3.0	EC000196
ETIM 4.0	EC000196
ETIM 5.0	EC000196

#### UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121515
UNSPSC 11	39121515
UNSPSC 12.01	39121515
UNSPSC 13.2	39121515

## Relay connectors - ST-REL2-KG 24/1AU - 2823722


approvals

---

GOST / GOST /

---

Approval details



Drawings

# Relay connectors - ST-REL2-KG 24/1AU - 2823722

Circuit diagram

