

# Diode block - EMG 22-DIO 4E-1N5408 - 2952790

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Diode module, with 4 diodes, individually wired, diode type 1N 5408

The illustration shows version EMG 22-DIO 4E

## Product Features

- Electrical decoupling of messages in fault reporting systems
- Spark-suppression diodes for limiting surge voltages of inductive loads



## Key commercial data

package_quantity	10
GTIN	4017918084486

## Technical data

### Dimensions

Width	22.5 mm
Height	75 mm
Depth	55 mm

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

### General

Diode type	1 N 5408
Max. operating voltage	250 V AC
Peak reverse voltage per diode	1000 V
Reverse current per diode	10 µA
Conducting state voltage per diode	approx. 0.8 V
Conducting state current per diode	1.5 A (with single load)
Conducting state current per diode	1 A (with simultaneous loads)
Surge voltage category	III, basic insulation (as per EN 50178)
Mounting position	Any
Assembly instructions	In rows with zero spacing

# Diode block - EMG 22-DIO 4E-1N5408 - 2952790

## Technical data

### Connection data

Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	4 mm <sup>2</sup>
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3
Connection method	Screw connection

## classifications

### eCl@ss

eCl@ss 4.0	27250312
eCl@ss 4.1	27260801
eCl@ss 5.0	27260801
eCl@ss 5.1	27260801
eCl@ss 6.0	27242602
eCl@ss 7.0	27242602
eCl@ss 8.0	27242602

### ETIM

ETIM 2.0	EC001432
ETIM 3.0	EC001597
ETIM 4.0	EC001597
ETIM 5.0	EC001596

### UNSPSC

UNSPSC 6.01	30211506
UNSPSC 7.0901	39121008
UNSPSC 11	39121008
UNSPSC 12.01	39121008
UNSPSC 13.2	39121008

## approvals

GOST /

### Approval details

--

# Diode block - EMG 22-DIO 4E-1N5408 - 2952790

accessories

EMG-GKS 12 - 2947035



---

## Drawings

Circuit diagram

