

Feed-through terminal block - PLC-VT/ACT - 2295567

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE feed-through terminal block (3-wire connection), for PLC-RELAY actuator series

The illustration shows version PLC-VT/ AKT/LA

Product Features

- Can be combined with PLC-INTERFACE actuator series
- With LED as an option
- Signal path with two additional potential levels for free assignment (three-wire connection)



Key commercial data

package_quantity	10
GTIN	4017918821852

Technical data

Dimensions

Width	6.2 mm
Height	80 mm
Depth	94 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

General

Nominal voltage U_N	max. 250 V AC/DC
Rated surge voltage	4 kV
Max. current carrying capacity per branch	6 A (per signal conductor)
Max. current carrying capacity per branch	6 A (per connection terminal block with jumper location)
Status display	No
Mounting position	Any
Assembly instructions	In rows with zero spacing
Standards/regulations	DIN EN 50178
Standards/regulations	IEC 62103

Feed-through terminal block - PLC-VT/ACT - 2295567

Technical data

General

Inflammability class according to UL 94	V0
Pollution degree	3
Surge voltage category	III

Connection data for connection 1

Connection name	Power supply
Connection in acc. with standard	IEC / EN
Number of connections	1
Connection method	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3

classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242208
eCl@ss 7.0	27242208
eCl@ss 8.0	27242208

ETIM

ETIM 2.0	EC001423
ETIM 3.0	EC001423
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC






UNSPSC 6.01	30211824
UNSPSC 7.0901	39121402
UNSPSC 11	39121402
UNSPSC 12.01	39121402
UNSPSC 13.2	39121402

Feed-through terminal block - PLC-VT/ACT - 2295567

approvals

UL Recognized / cUL Recognized / GOST / GL / cULus Recognized /

Approval details



accessories

Mounting rail

NS 35/ 7,5 V2A UNPERF 2000MM - 0801377



NS 35/ 7,5 PERF 2000MM - 0801733



Feed-through terminal block - PLC-VT/ACT - 2295567

accessories

NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15-2,3 UNPERF 2000MM - 1201798



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 PERF 2000MM - 1201730



Feed-through terminal block - PLC-VT/ACT - 2295567

accessories

NS 35/ 7,5 UNPERF 2000MM - 0801681



Power module

PLC-ESK GY - 2966508



Partition plate

PLC-ATP BK - 2966841



Screwdriver tools

SZF 1-0,6X3,5 - 1204517



Labeled terminal marker

Feed-through terminal block - PLC-VT/ACT - 2295567

accessories

ZB 6,LGS:FORTL.ZAHLEN - 1051016



Terminal marking

ZB 6:UNBEDRUCKT - 1051003



Controller board

PLC-V8/FLK14/OUT - 2295554



PLC-V8/FLK14/OUT/M - 2304102



PLC-V8/D15B/OUT - 2296061



Interface module

Feed-through terminal block - PLC-VT/ACT - 2295567

accessories

PLC-V8/D15S/OUT - 2296058



Bridge

FBST 500-PLC RD - 2966786



FBST 500-PLC BU - 2966692



FBST 500-PLC GY - 2966838



FBST 6-PLC RD - 2966236



Feed-through terminal block - PLC-VT/ACT - 2295567

accessories

FBST 6-PLC BU - 2966812



FBST 6-PLC GY - 2966825




FBST 8-PLC GY - 2967688



Drawings

Circuit diagram



PLC-VT/ACT connection scheme