# PB-1220PF-01Q


(ROHS)

DATE:2005.01.21


<b>1</b> □ Electrical Characteristics	VER .:0	
Oscillation Frequency (Hz)	2048	
Operating Voltage (Vdc)	1.25 ~ 2.5	
Rated Voltage (Vdc)	1.5	
Current Consumption (mA/max.)	40 at Rated Voltage	
Sound Pressure Level (dB/min.)	88 at 10cm at Rated Voltage	
Coil Resistance (Ω)	16 ± 2	
Operating Temperature (°C)	<b>-</b> 20 ∼ +60	
Storage Temperature (℃)	<b>-</b> 30 ∼ +80	
Wave soldering conditions	245±5°C for 3±0.5 seconds.	
Manual soldering conditions	350±20°C / within 5sec	

PS: Vp-p=1/2duty, square wave

### **2**□Typical Frequency Response Curve



# **3**□Dimensions and Material **3-1** Shape




Unit: mm **3-2** 

#### Material

Housing	PPO plastic resin (Color : Black)
Leading Pin	Tin Plated Brass
Weight (Gram)	1.3

## **4**□Recommend Driving Circuit



The base current Ib should high enough so that it saturates the collector current of the transistor with the CB load.


#### 5. TESTING METHOD

#### Standard Measurement conditions


Temperature:25± 2°C Humidity:45-60%

#### . Acoustic Characteristics

The oscillation frequency, current consumption and sound pressure are measured by the measuring instruments shown below.



In the measuring test, buzzers is placed as follows:



#### 6. RELIABILITY

ITEMS	METHOD OF TEST AND MEASUREMENTS	PERFORMANCE
Coldness withstanding	After 98 hours of being exposed to -30°C environment, should be returned to normal environment for 2 hours, then re-proceed to test.	No abnormality shall exist
Hotness withstanding	After 98 hours of being exposed to +80°C environment, should be returned to normal environment for 2 hours, then re-proceed to test.	No abnormality shall exist
Humidity withstanding	After 98 hours of being exposed to 40°C 95%RH environment in actual operation, should be returned to normal environment for 2 hours, then re-proceed to test.	No abnormality shall exist
Durability	Testing after 1,000 hours actual continuous operation. (at standard measurement conditions)	No abnormality shall exist
Drop withstanding	A natural drop from 75cm high down to the ground.	No abnormality shall exist
Vibration withstanding	Vibration of 2,000 cycles per minute, 2mm amplitude, applied in X, Y and Z directions for 30 minutes each.	No abnormality shall exist

#### 7. PACKAGE METHOD

< 1 > 100pcs per box , Total 10 boxes per carton , total 1000pcs carton; Volume: L\*W\*H=510\*330\*300mm

#### < 2 > RoHS Mark

