

Datasheet


Item no. 701810/ 701825/ 701811/ 701812/ 701826/ 701813/
701814/ 701824

V1_0717_01_en

Metal (illuminated) selector



- ⊙ Φ 19mm diameter
- ⊙ Switch Rating: 5A/250VAC
- ⊙ Contact Configuration: 1NO1NC / 2NO 2NC
- ⊙ Two Position Remain / Three Position Remain
- ⊙ The crust material: Stainless Steel
- ⊙ Arrowhead Illuminated
- ⊙ IP Degree: IP67



701810 : Metal selector, Dia.19mm, 1NO1NC, 2 position Maintain, Stainless steel, 250 V AC imprint

701825 : Metal (illuminated) selector (blue color), Dia.19mm, 1NO1NC, 2 position Maintain, Blue 12V LED, Stainless steel, 250 V AC imprint

701811 : Metal (illuminated) selector (white color), Dia.19mm, 1NO1NC, 2 position Maintain, White 12V LED, Stainless steel, 250 V AC imprint

701812 : Metal selector, Dia.19mm, 2NO2NC, 3 position Maintain, Stainless steel, 250 V AC imprint


701826 : Metal (illuminated) selector (blue color), Dia.19mm, 2NO2NC, 3 position Maintain, Blue 12V LED, Stainless steel, 250 V AC imprint

701813 : Metal (illuminated) selector (white color), Dia.19mm, 2NO2NC, 3 position Maintain, White 12V LED, Stainless steel, 250 V AC imprint

Metal keylock switch



- ⊙ Φ 19mm diameter
- ⊙ Switch Rating: 5A/250VAC
- ⊙ Contact Configuration: 1NO1NC / 2NO 2NC
- ⊙ Two Position Remain / Three Position Remain
- ⊙ The crust material: Stainless Steel
- ⊙ IP Degree: IP65
















701814 : Dia.19mm, 1NO1NC, 2 position Maintain, Stainless steel, 250 V AC imprint

701824 : Dia.19mm, 2NO2NC, 3 position Maintain, Stainless steel, 250 V AC imprint

Datasheet

Item no. 701810/ 701825/ 701811/ 701812/ 701826/ 701813/
701814/ 701824

V1_0717_01_en

Item no.		701810 701825 701811	701812 701826 701813	701814 701824	
The Front Shape		Selector		Key Lock	
Terminal Type		Pin Terminal(2.8×0.5mm)		Pin Terminal(2.8×0.5mm)	
Switching		No.3		No.3	
Max.Switch Rating		Ith:5A Ui:250VAC		Ith:5A Ui:250VAC	
Contact Resistance		≤ 50mΩ		≤ 50mΩ	
Insulation Resistance		≥ 1000MΩ		≥ 1000MΩ	
Dielectric Intensity		2000VAC		2000VAC	
Operating Temp		-20°C ~ +55°C		-20°C ~ +55°C	
Mechanical life		500,000cycles		500,000cycles	
Electrical life		50,000cycles		50,000cycles	
Panel Thickness		1 ~ 10mm		1 ~ 10mm	
Torque		5 ~ 14Nm		5 ~ 14Nm	
IP Degree		IP67		IP65	
Material	Contact	Silver Alloy		Silver Alloy	
	Button	Stainless Steel		Stainless Steel	
	Body	Stainless Steel		Stainless Steel	
	Base	PBT		PBT	
	RoHS	Yes		Yes	
LED Spec.	Type	Arrowhead(LED)		---	
	Rated Voltage	6V / 12V / 24V / 110V / 220V		---	
	Color	R G Y O B W		---	
	Life	40000 hours		---	
LAS1-AGQ State chart in operation	Position	Contact	Left	Center	Right
	90° Two position	1NO1NC			
		2NO2NC	 		 
45° 3 Three position	2NO2NC	 	 	 	

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

© Copyright 2017 by Conrad Electronic SE.