

**SAFETY DATA SHEET**

713044 WHITEBOARD CLEANER 250 ML

Page: 1

Compilation date: 17.04.2014

Revision No: 1

**Section 1: Identification of the substance/mixture and of the company/undertaking**

**1.1. Product identifier**

**Product name:** 713044 WHITEBOARD CLEANER 250 ML

**Product code:** DF1685

**Synonyms:** L03000000094

**1.2. Relevant identified uses of the substance or mixture and uses advised against**

**Use of substance / mixture:** PC35: Washing and cleaning products (including solvent based products).

**1.3. Details of the supplier of the safety data sheet**

**Company name:** KLEINMANN GmbH

Am Trieb 13

D - 72820 Sonnenbühl

Deutschland

**Tel:** +49(0)7128-9292-0

**Fax:** +49 (0)7128-929292

**Email:** chemie@kleinmann.net

**1.4. Emergency telephone number**

**Emergency tel:** +49 (0)7128-929215

(office hours only)

**Section 2: Hazards identification**

**2.1. Classification of the substance or mixture**

**Classification under CLP:** -: EUH208

**Classification under CHIP:** This product has no classification under CHIP.

**2.2. Label elements**

**Label elements under CLP:**

**Hazard statements:** EUH208: Contains orangenÖl. May produce an allergic reaction.

**Precautionary statements:** P102: Keep out of reach of children.

P103: Read label before use.

P101: If medical advice is needed, have product container or label at hand.

P302+352: IF ON SKIN: Wash with plenty of soap and water.

P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

**2.3. Other hazards**

**PBT:** This product is not identified as a PBT/vPvB substance.

# SAFETY DATA SHEET

713044 WHITEBOARD CLEANER 250 ML

Page: 2

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

#### Hazardous ingredients:

PROPAN-2-OL

EINECS	CAS	CHIP Classification	CLP Classification	Percent
200-661-7	67-63-0	F: R11; Xi: R36; -: R67	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336	1-10%

2-BUTOXYETHANOL

203-905-0	111-76-2	Xn: R20/21/22; Xi: R36/38	Acute Tox. 4: H332; Acute Tox. 4: H312; Acute Tox. 4: H302; Eye Irrit. 2: H319; Skin Irrit. 2: H315	1-10%
-----------	----------	---------------------------	---	-------

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Wash immediately with plenty of soap and water.

**Eye contact:** Bathe the eye with running water for 15 minutes. Consult a doctor.

**Ingestion:** Wash out mouth with water. If conscious, give half a litre of water to drink immediately.  
Consult a doctor.

**Inhalation:** Not applicable.

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be mild irritation at the site of contact.

**Eye contact:** There may be irritation and redness.

**Ingestion:** No data available.

**Inhalation:** No data available.

**Delayed / immediate effects:** No data available.

### 4.3. Indication of any immediate medical attention and special treatment needed

**Immediate / special treatment:** Not applicable.

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

[cont...]

# SAFETY DATA SHEET

713044 WHITEBOARD CLEANER 250 ML

Page: 3

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Refer to section 8 of SDS for personal protection details. Turn leaking containers leak-side up to prevent the escape of liquid.

### 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers. Contain the spillage using bunding.

### 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

### 6.4. Reference to other sections

**Reference to other sections:** Refer to section 8 of SDS.

## Section 7: Handling and storage

### 7.1. Precautions for safe handling

**Handling requirements:** Not applicable.

### 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Store in cool, well ventilated area. Keep container tightly closed.

**Suitable packaging:** Must only be kept in original packaging.

### 7.3. Specific end use(s)

**Specific end use(s):** No data available.

## Section 8: Exposure controls/personal protection

### 8.1. Control parameters

**Hazardous ingredients:**

**PROPAN-2-OL**

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	999 mg/m <sup>3</sup>	1250 mg/m <sup>3</sup>	-	-

**2-BUTOXYETHANOL**

UK	25 ppm	50 ppm	-	-
----	--------	--------	---	---

### 8.1. DNEL/PNEC Values

**DNEL / PNEC** No data available.

### 8.2. Exposure controls

**Engineering measures:** Not applicable.

[cont...]

# SAFETY DATA SHEET

713044 WHITEBOARD CLEANER 250 ML

Page: 4

**Respiratory protection:** Respiratory protection not required.

**Hand protection:** Nitrile gloves. Breakthrough time of the glove material > 4 hours.

**Eye protection:** Safety glasses. Ensure eye bath is to hand.

**Skin protection:** Protective clothing.

**Environmental:** Not applicable.

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**State:** Liquid

**Colour:** Colourless

**Odour:** Barely perceptible odour

**Relative density:** 0,985

**pH:** 7,5

**VOC g/l:** 83,79

### 9.2. Other information

**Other information:** No data available.

## Section 10: Stability and reactivity

### 10.1. Reactivity

**Reactivity:** Stable under recommended transport or storage conditions.

### 10.2. Chemical stability

**Chemical stability:** Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

**Hazardous reactions:** Hazardous reactions will not occur under normal transport or storage conditions.  
Decomposition may occur on exposure to conditions or materials listed below.

### 10.4. Conditions to avoid

**Conditions to avoid:** Heat.

### 10.5. Incompatible materials

**Materials to avoid:** Strong oxidising agents. Strong acids.

### 10.6. Hazardous decomposition products

**Haz. decomp. products:** In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

[cont...]

# SAFETY DATA SHEET

713044 WHITEBOARD CLEANER 250 ML

Page: 5

## Hazardous ingredients:

### PROPAN-2-OL

DERMAL	RBT	LD50	12800	mg/kg
ORAL	RAT	LD50	5050	mg/kg

### 2-BUTOXYETHANOL

IVN	RAT	LD50	307	mg/kg
ORL	MUS	LD50	1230	mg/kg
ORL	RAT	LD50	470	mg/kg

**Toxicity values:** No data available.

## Symptoms / routes of exposure

**Skin contact:** There may be mild irritation at the site of contact.

**Eye contact:** There may be irritation and redness.

**Ingestion:** No data available.

**Inhalation:** No data available.

**Delayed / immediate effects:** No data available.

## Section 12: Ecological information

### 12.1. Toxicity

#### Hazardous ingredients:

### PROPAN-2-OL

FISCH	96H LC50	9640	mg/l
-------	----------	------	------

### 12.2. Persistence and degradability

**Persistence and degradability:** Biodegradable.

### 12.3. Bioaccumulative potential

**Bioaccumulative potential:** No bioaccumulation potential.

### 12.4. Mobility in soil

**Mobility:** Readily absorbed into soil.

### 12.5. Results of PBT and vPvB assessment

**PBT identification:** This product is not identified as a PBT/vPvB substance.

### 12.6. Other adverse effects

**Other adverse effects:** Negligible ecotoxicity.

## Section 13: Disposal considerations

[cont...]

# SAFETY DATA SHEET

713044 WHITEBOARD CLEANER 250 ML

Page: 6

## 13.1. Waste treatment methods

**Disposal operations:** No data available.

**Recovery operations:** Not applicable.

**Disposal of packaging:** Dispose of as normal industrial waste.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

## Section 14: Transport information

**Transport class:** This product does not require a classification for transport.

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

**Specific regulations:** Not applicable.

### 15.2. Chemical Safety Assessment

**Chemical safety assessment:** A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

## Section 16: Other information

### Other information

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

\* indicates text in the SDS which has changed since the last revision.

This safety data sheet is prepared in accordance with Commission Regulation (EC) No 1272/2008.

**Phrases used in s.2 and 3:** EUH208: Contains <name of sensitising substance>. May produce an allergic reaction.

H225: Highly flammable liquid and vapour.

H302: Harmful if swallowed.

H312: Harmful in contact with skin.

H315: Causes skin irritation.

H319: Causes serious eye irritation.

H332: Harmful if inhaled.

H336: May cause drowsiness or dizziness.

R11: Highly flammable.

R20/21/22: Harmful by inhalation, in contact with skin and if swallowed.

R36/38: Irritating to eyes and skin.

R36: Irritating to eyes.

R67: Vapours may cause drowsiness and dizziness.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.