

Control cabinet marker - SSMK 60X18 - 5032439

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Control cabinet marker, size: 60 x 18 mm, lettering field: 56 x 14 mm, 2 mounting holes M3, including 1 x ES-SSMK-GB 60 x 18

Product Features

- ✓ The ES-SSMK ... insert strips can be labeled using the CMS-P1-PLOTTER and the CMS-P1-PAD magazine
- ✓ The labeling is resistant to external influences
- ✓ The base carrier has two fixing holes so that it can be screwed on
- ✓ Control cabinet markers consisting of a transparent cap and base carrier
- ✓ Once labeled, the insert label is inserted in the cap and this is then snapped onto the base carrier

Key commercial data

package_quantity	50
GTIN	4017918095802

Technical data

Dimensions

Length (b)	60 mm
Width (a)	18 mm
Hole diameter	3.50 mm
Drill hole spacing	40.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
---------------------------------	-------------------

General

Note	Can be labeled with CMS
Color	transparent/white
Base element material	PC
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	PC

classifications

eCl@ss

eCl@ss 4.0	24190218
------------	----------

Control cabinet marker - SSMK 60X18 - 5032439

classifications

eCl@ss

eCl@ss 4.1	24190218
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Device marking

ES-SSMK-GB 60X18 - 5032468



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>