DATASHEET - LS-S11/RLA



Position switch, Adjustable roller lever, Complete unit, 1 N/O, 1 NC, Screw terminal, Yellow, Insulated material, -25 - +70 $^{\circ}$ C

Powering Business Worldwide*

Part no. LS-S11/RLA Catalog No. 106790 Alternate Catalog LS-S11-RLA

No.

EL-Nummer 4315208

(Norway)

Delivery program

Delivery program		
Basic function		Position switches Safety position switches
Part group reference		LS(M)
Product range		Adjustable roller lever
Degree of Protection		IP66, IP67
Features		Complete unit
Ambient temperature	°C	-25 - +70
Contacts		
N/0 = Normally open		1 N/O
N/C = Normally closed		1 NC →
Notes		e safety function, by positive opening to IEC/EN 60947-5-1
Contact sequence		0-\frac{13}{14}\frac{1}{22}
Contact travel = Contact closed = Contact open		0° 46° 65° 13-14 21-22 NC 32° Zw = 48°
Positive opening (ZW)		yes
Colour		
Enclosure covers		Yellow
Enclosure covers		
Housing		Insulated material
Connection type		Screw terminal
Notes The operating head can be rotated at 90° intervals to adapt to the specified approach direction.		

Technical data

General

Standards		IEC/EN 60947
Climatic proofing		Damp heat, constant, to IEC 60068-2-78; damp heat, cyclical, to IEC 60068-2-30
Ambient temperature	°C	-25 - +70
Mounting position		As required

			IDOG IDOT	
Degree of Protection			IP66, IP67	
Terminal capacities		mm ²		
Solid		mm ²	1 x (0.5 - 2.5)	
Flexible with ferrule		mm^2	1 x (0.5 - 1.5)	
Repetition accuracy		mm	0.15	
Contacts/switching capacity				
Rated impulse withstand voltage	U_{imp}	V AC	4000	
Rated insulation voltage	Ui	V	400	
Overvoltage category/pollution degree			III/3	
Rated operational current	l _e	Α		
AC-15				
24 V	Ie	Α	6	
220 V 230 V 240 V	I _e	Α	6	
380 V 400 V 415 V	I _e	Α	4	
DC-13				
24 V	le	Α	3	
110 V	I _e	Α	0.6	
220 V	I _e	A	0.3	
Control circuit reliability	-			
at 24 V DC/5 mA	H _F	Fault probabili	< 10 ⁻⁷ , < 1 fault in 10 ⁷ operations	
at 5 V DC/1 mA	H _F	Fault probabili	$< 5 \times 10^{-6}$, < 1 failure at 5×10^{6} operations	
Supply frequency		Hz	max. 400	
Short-circuit rating to IEC/EN 60947-5-1				
max. fuse		A gG/gL	6	
Rated conditional short-circuit current		kA	1	
Mechanical variables				
Lifespan, mechanical	Operations	x 10 ⁶	8	
Mechanical shock resistance (half-sinusoidal shock, 20 ms)				
Standard-action contact		g	25	
Operating frequency	Operations/h		≦ 6000	
Actuation				
Mechanical				
Actuating force at beginning/end of stroke		N	1.0/8.0	
Actuating torque of rotary drives		Nm	0.2	
Max. operating speed with DIN cam		m/s	1.5	
Notes			for angle of actuation α = 30°, L = 125 mm	

Design verification as per IEC/EN 61439

In	Α	6
P _{vid}	W	0.17
P _{vid}	W	0
P_{vs}	W	0
P _{diss}	W	0
	°C	-25
	°C	70
		Meets the product standard's requirements.
		Meets the product standard's requirements.
		Meets the product standard's requirements.
		Meets the product standard's requirements.
	P _{vid} P _{vid} P _{vs}	P _{vid} W P _{vid} W P _{vs} W P _{diss} W °C

10.2.4 Resistance to ultra-violet (UV) radiation	Meets the product standard's requirements.
10.2.5 Lifting	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions	Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances	Meets the product standard's requirements.
10.5 Protection against electric shock	Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components	Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections	Is the panel builder's responsibility.
10.8 Connections for external conductors	Is the panel builder's responsibility.
10.9 Insulation properties	
10.9.2 Power-frequency electric strength	Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage	Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material	Is the panel builder's responsibility.
10.10 Temperature rise	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 7.0

Sensors (EG000026) / End switch (EC000030)

Electric engineering, automation, process control engineering / Binary sensor technology, safety-related sensor technology / Position switch / Position switch (Type 1)


(ecl@ss10.0.1-27-27-06-01 [AGZ382015])		
Width sensor	mm	31
Diameter sensor	mm	0
Height of sensor	mm	61
Length of sensor	mm	33.5
Rated operation current le at AC-15, 24 V	А	6
Rated operation current le at AC-15, 125 V	Α	6
Rated operation current le at AC-15, 230 V	Α	6
Rated operation current le at DC-13, 24 V	Α	3
Rated operation current le at DC-13, 125 V	Α	0.8
Rated operation current le at DC-13, 230 V	Α	0.3
Switching function		Slow-action switch
Switching function latching		No
Output electronic		No
Forced opening		Yes
Number of safety auxiliary contacts		1
Number of contacts as normally closed contact		1
Number of contacts as normally open contact		1
Number of contacts as change-over contact		0
Type of interface		None
Type of interface for safety communication		None
Construction type housing		Cuboid
Material housing		Plastic
Coating housing		Other
Type of control element		Adjustable roller lever
Alignment of the control element		Other
Type of electric connection		Other
With status indication		No
Suitable for safety functions		Yes
Explosion safety category for gas		None
Explosion safety category for dust		None

Ambient temperature during operating	°C	25 - 70
Degree of protection (IP)		IP67
Degree of protection (NEMA)		4X

Approvals

Product Standards	IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14; CE marking
UL File No.	E29184
UL Category Control No.	NKCR
CSA File No.	12528
CSA Class No.	3211-03
North America Certification	UL listed, CSA certified
Degree of Protection	IEC: IP66, 67, UL/CSA Type 3R, 4X (indoor use only), 12, 13

Dimensions



- ① Tightening torque of cover screws: 0.8 Nm \pm 0.2 Nm ② only with LS (insulated version) ③ Fixing screws $2 \times M4 \ge 30$ $M_A = 1.5$ Nm

