

Marker strip - SK 3,8 WH:REEL - 0805218

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Marker strip, Roll, white, Unlabeled, Can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, Mounting type: Adhesive

Product Features

- The SK labeling range offers self-adhesive marker strips for labeling products that do not have a marker groove
- Labeling service: Phoenix Contact can custom-label SK markers according to your requirements
- The SK labeling range offers self-adhesive marker strips for labeling products that do not have a marker groove

Key commercial data

package_quantity	1
GTIN	4017918309091

Technical data

Dimensions

Length (b)	90 m
Width (a)	3.8 mm
Inner diameter (f)	76.00 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 150 °C

General

Color	white
Base element material	Polyester
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	Polyester
Number of individual labels	210000
Number of individual labels per row	10
Number of marker strips	14

classifications

eCl@ss

eCl@ss 4.0	24190208
-------------------	----------

Marker strip - SK 3,8 WH:REEL - 0805218

classifications

eCl@ss

eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Marker pen

B-STIFT - 1051993



Ink ribbon

THERMOMARK-RIBBON 110 - 5145384



Drawings