

# V4N

## Snap-action Microswitches

Subminiature

### V4N


Characteristics ■ sealed (IP67)  
 ■ solder, 2.8 mm faston and PCB terminals  
 ■ pre-wired option

Rating 250 VAC, 5 A

Dimensions (mm) 20 × 10.3 × 6.4

Actuator ■ plunger  
 ■ plain levers  
 ■ roller levers  
 ■ simulated roller lever/cam follower

Approvals UL, CSA, ENEC




### Preferred Range

Ordering Reference	Actuating Force		Sealing	Operating pos.		Terminal	Circuit	Actuator	Contacts	Electrical rating
	(N)	(ozf)		(mm)	(in)					
V4NT7UL	1.40	5.0	IP40	8.40	0.33	Solder	CO	Plain plunger	Ag	250 VAC, 5 A
V4NST7UL	2.50	9.0	IP67	8.40	0.33	Solder	CO	Plain plunger	Ag	250 VAC, 5 A
V4NSUL	2.50	9.0	IP67	8.40	0.33	Pre-wired	CO	Plain plunger	Ag	250 VAC, 5 A
V4NT7Y1UL	0.50	1.8	IP40	10.7	0.42	Solder	CO	Straight lever	Ag	250 VAC, 5 A
V4NST7Y1UL	0.90	3.2	IP67	10.6	0.42	Solder	CO	Straight lever	Ag	250 VAC, 5 A
V4NSY1UL	0.90	3.2	IP67	10.6	0.42	Pre-wired	CO	Straight lever	Ag	250 VAC, 5 A
V4NT7YRUL	0.50	1.8	IP40	15.7	0.62	Solder	CO	Roller lever	Ag	250 VAC, 5 A
V4NST7YRUL	0.90	3.2	IP67	15.6	0.62	Solder	CO	Roller lever	Ag	250 VAC, 5 A
V4NSYRUL	0.90	3.2	IP67	15.6	0.62	Pre-wired	CO	Roller lever	Ag	250 VAC, 5 A


## Specifications

Housing	Flame-retardant glass-fibre reinforced nylon
Plunger	Polyacetal (POM)
Mechanism	Snap-action coil spring mechanism with stainless steel spring
Functions	Change-over, normally closed or normally open
Contacts	Silver
Terminals	Gold flashed
Temperature range °C	-40°C to +85°C
Mechanical life	5 × 10 <sup>6</sup> cycles minimum (impact free actuation) for the cowl 3 × 10 <sup>6</sup>
Protection	IP40 (V4N - enclosure), IP67 (V4NS - enclosure)
Mounting	Side mounting
Actuators	Plain lever, cam follower, Roller lever
Accessories	Insulating sheet - N04619, Clip-on terminal cover - TC102, Long overtravel actuator - QA4

Circuit diagram







Dimensions



## Recommended maximum electrical ratings

	Voltage (max)	Load (A)	Inductive load (A)	Approval
V4NT7UL/ V4NST7UL	250 VAC	5 (0.75 pf)		UL 1054/CSA 22.2 No. 55 - 6,000 operations - 65°C EN61058-1, T85, 10,000 operations
	250 VAC	5	2	
	0 - 15 VDC	5	3	
	15 - 30 VDC	5	3	General rating - 50,000 operations (85°C) General rating - 50,000 operations (85°C)
V4NSUL	250 VAC	3 (0.75 pf)		UL 1054/CSA 22.2 No. 55 - 6,000 operations - 65°C EN61058-1, T85, 10,000 operations
	250 VAC	5	2	
	0 - 15 VDC	3	3	
	15 - 30 VDC	3	3	

Operating Characteristics

Actuator	Reference	Actuating Force Maximum		Release Force Minimum		Free Position Maximum		Operating Position		Movement Differential Maximum	
		(N)	(ozf)	(N)	(ozf)	(mm)	(in)	(mm)	(in)	(mm)	(in)
Plunger 	V4NT7UL	1,4	5,00	0,28	1,00	9,2	0,36	8,4 ± 0,3	0,33 ± 0,012	0,1	0,004
	V4NST7UL	2,5	9,00	0,30	1,00	9,2	0,36	8,4 ± 0,3	0,33 ± 0,012	0,1	0,004
	V4NSUL	2,5	9,00	0,3	1,00	9,2	0,36	8,4 ± 0,3	0,33 ± 0,012	0,1	0,004
Y1 lever 	V4NT7Y1UL	0,5	1,80	0,07	0,25	13,2	0,52	10,7 ± 1,0	0,42 ± 0,04	0,4	0,016
	V4NST7Y1UL	0,9	3,20	0,07	0,25	13,2	0,52	10,6 ± 1,2	0,42 ± 0,05	0,4	0,016
	V4NSY1UL	0,9	3,20	0,07	0,25	13,2	0,52	10,6 ± 1,2	0,42 ± 0,05	0,4	0,016
Width of lever 4.0 mm/0.16 in											
YC lever 	V4NT7YCUL	0,5	1,80	0,07	0,25	17,8	0,70	15,7 ± 1,0	0,62 ± 0,04	0,4	0,016
	V4NST7YCUL	0,9	3,20	0,07	0,25	17,8	0,70	15,6 ± 1,2	0,61 ± 0,05	0,4	0,016
	V4NSYCUL	0,9	3,20	0,07	0,25	17,8	0,70	15,6 ± 1,2	0,61 ± 0,05	0,4	0,016
Width of lever 4.0 mm/0.16 in											
YR lever 	V4NT7YRUL	0,5	1,80	0,07	0,25	17,8	0,70	15,7 ± 1,0	0,62 ± 0,04	0,4	0,016
	V4NST7YRUL	0,9	3,20	0,07	0,25	17,8	0,70	15,6 ± 1,2	0,61 ± 0,05	0,4	0,016
	V4NSYRUL	0,9	3,20	0,07	0,25	17,8	0,70	15,6 ± 1,2	0,61 ± 0,05	0,4	0,016
Width of lever 4.0 mm/0.16 in											

Over travel: Plunger can be depressed flush with housing. The housing should not be used as an end stop.

Type coding key for standard products

Basic type	V4N	Example: V4N	E	T6	C2	Y1	0	G	UL
Type of sealing/ Overtravel	No symbol, unsealed, standard travel								
E	Unsealed with extended overtravel (0.5 mm)								
S	Sealed IP67 standard travel								
B	Sealed IP67 with extended overtravel (0.5 mm)								
Terminals	No symbol, pre-wired 500 mm with cable box K2 (V4NS/B only)								
T6	Faston	2.03 × 0.5 × 6.6 long							
T7	Solder	2.95 × 0.5 × 3.6 long							
T8	PCB	0.8 × 0.5 × 4.0 long							
T9	Faston	2.8 × 0.5 × 8.1 long							
T81	Formed PCB	0.8 × 0.5 × 3.8 long							
T82	Formed PCB	0.8 × 0.5 × 3.8 long							
T83	Formed PCB	8.8 × 0.5 × Surface mount							
T84	Short PCB	0.8 × 0.5 × 2.0 long							
T85	Long PCB	0.8 × 0.5 × 6.85 long							
T86	PCB	0.8 × 0.5 × 4.0 long (equi-spaced)							
T11	Solder	2.95 × 0.5 × 3.6 long							
Circuit	No symbol, change-over								
C2	Normally closed								
C4	Normally open								
Actuators	No symbol, without lever								
Y1	Plain lever	18.0 mm							
Y2	Plain lever	25.0 mm							
Y3	Plain lever	32.0 mm							
YC	Cam follower lever	18.5 mm							
YR	Roller lever	16.0 mm							
PB	Push Button	(see specification PBA4/QA4)							
QA	Push Button	(see specification PBA4/QA4)							
Other actuators on special request									
Actuator Position	No symbol, without lever, or lever fitted at the end nearest to the Plunger								
0	With lever fitted at end opposite to plunger								
Contact Material	No symbol, Fine silver								
G	Gold plate on silver								
X	Gold alloy on silver palladium crosspoint								
Approvals	No symbol, without approval								
UL	UL, CSA and ENEC approval								
Special Features	/ <input type="checkbox"/> <input type="checkbox"/> <input type="checkbox"/> <input type="checkbox"/> Saia-Burgess specialise in customer specific solutions. Additional product variants are available or can be provided. If your requirements cannot be satisfied from the options listed, please contact <a href="http://www.saia-burgess.com">www.saia-burgess.com</a> or your local SB outlet.								