

# Adapter cable - CABLE-15/8/250/RSM/KINETIX - 2986698

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable adapter for PSR speed monitors (PSR-RSM4 and PSR-MOTIONSTOP), 15/8-pos., cable length: 2.5 m, for controller: Allen-Bradley (Kinetix)

## Product Features

- Option to connect to PSR-RSM4 and PSR-MOTIONSTOP safe speed monitors
- Suitable for connection to the existing motor feedback interface of an electrical drive
- Controller type: AB Kinetix
- 15-pos. D-SUB connection (HD)
- Length of connecting cable to speed monitor: 250 cm

## Key commercial data

package_quantity	1
GTIN	4046356608206

## Technical data

### Dimensions

Fixed cable length	2.5 m
--------------------	-------

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C (for fixed installation)
Ambient temperature (operation)	0 °C ... 50 °C (for flexible installation)
Ambient temperature (storage/transport)	-20 °C ... 70 °C

### General

Connection 1	To the device
Connection method	RJ45
Connection method	D-SUB-15 male/D-SUB-15 female
Number of positions	15
Cable resistance	≤ 260 Ω/km
Conductor material	Bare Cu litz wires
Shielding	Plastic-coated aluminum foil, tinned copper braided shield
Shielding	Soldering on D-SUB housing
Conductor cross section	0.48 mm <sup>2</sup> (AWG 26)

## Adapter cable - CABLE-15/8/250/RSM/KINETIX - 2986698

### classifications

#### eCl@ss

<b>eCl@ss 4.0</b>	27060307
<b>eCl@ss 4.1</b>	27060307
<b>eCl@ss 5.0</b>	27060307
<b>eCl@ss 5.1</b>	27371901
<b>eCl@ss 6.0</b>	27371819
<b>eCl@ss 7.0</b>	27371819
<b>eCl@ss 8.0</b>	27371819

#### ETIM

<b>ETIM 3.0</b>	EC000467
<b>ETIM 4.0</b>	EC001449
<b>ETIM 5.0</b>	EC000467

#### UNSPSC

<b>UNSPSC 6.01</b>	30211901
<b>UNSPSC 7.0901</b>	39121501
<b>UNSPSC 11</b>	39121501
<b>UNSPSC 12.01</b>	39121501
<b>UNSPSC 13.2</b>	39121501

### Drawings