

## Data sheet

### Article Description

#### Line Intermediate Switch Type 5055

3 (2) A, 250 V~, 1-pole, on/off-switch


catch locking housing,  
strain relief by insulant screws,

- for cables H03VV-F 2 x 0,50 mm<sup>2</sup> or 2 x 0,75 mm<sup>2</sup>
- degree of protection IP40
- screw terminals (Suitability for terminals for connecting unprepared conductors)
- LWH 67 x 22 x 17 mm

**Suitable for LED!!!**

Height with rocker: 17 mm  
Height without rocker: 15 mm  
Diameter rocker: 15 mm

### Article Picture



<i>inter BÄR-item no.</i>	<i>Colour housing</i>	<i>rocker</i>
5055-004...	black	black
5055-008...	white	white
5055-009...	brown	brown
5055-010...	gold	gold
5055-020...	titan	black

**Technical modifications reserved!**

**Works at 230 V-mains must only be carried out by a specialist!**