

Marker for terminal blocks - UCT-TM 6 - 0828736

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Marker for terminal blocks, Sheet, white, Unlabeled, Can be labeled with: THERMOMARK CARD PLUS, THERMOMARK CARD, BLUEMARK CLED, BLUEMARK LED, Mounting type: Snap into tall marker groove, For terminal block width: 6.2 mm, Lettering field: 5.6 x 10.5 mm

Product Features

- ✓ The multi-section marking strips are easy to fit and can be easily separated if required
- ✓ Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- ✓ The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and precisely using the THERMOMARK CARD and the BLUEMARK LED
- ✓ The sheets provide space for including function texts
- ✓ The UCT-TM... UniCard labeling range includes markers for products with tall marker grooves

Key commercial data

package_quantity	10
GTIN	4046356522465

Technical data

Dimensions

Length (b)	10.5 mm
Height	4.76 mm
Width (a)	5.6 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 120 °C

General

Note	Can be labeled via thermal transfer
Color	white
Components	free from silicone and halogen
Inflammability class according to UL 94	V0
Material	PC
Number of individual labels	60
Number of individual labels per row	10
RoHS compliant	Yes
Printability	Thermal transfer
Printability	Inkjet printing

Marker for terminal blocks - UCT-TM 6 - 0828736

Technical data

General

Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:1997-06
Climate level	KFW 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	IEC 61010-1:2010-06
Result	Test passed

classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Magazine

Marker for terminal blocks - UCT-TM 6 - 0828736

accessories

THERMOMARK CARD-UCT-MAG1 - 5146480



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>