



STANDARD 4 KEYPAD



1+4 MATRIX KEYPAD WITH INSERT POCKET

APEM COMPONENTS



RoHS COMPLIANT

MECHANICAL SPECIFICATIONS:


CONTACT FORCE 400 grams.
TRAVEL 0.80 TO 0.90 mm.

ELECTRICAL SPECIFICATIONS:

CONTACT VOLTAGE RATING 30V (dc).
CONTACT CURRENT RATING 100mA.
INSULATION RESISTANCE AT 100 V >100 Mohms.
DIELECTRIC STRENGTH 250 V rms.
CAPACITANCE 10 pF typ.
CONTACT BOUNCE BELOW 10 msec. typ.

ENVIRONMENTAL SPECIFICATIONS:

OPERATING TEMPERATURE -30 TO +55 C.
STORAGE TEMPERATURE -40 TO +60 C.



2 INSERTS WITH BLACK GRAPHICS ON A SILVER BACKGROUND SUPPLIED WITH THIS KEYPAD.
FOR OTHER VARIANTS OF INSERTS PLEASE CALL APEM

